UniStrip G4

ZCP383 L50 glare shield (15 pcs)

Accessory, UniStrip G4

UniStrip G4 is a surface mounted, exterior-rated LED luminaire that is designed for façade and outdoor architectural lighting applications. One family that fits all your needs, wall washing, grazing and also linear flood lighting. The robust mechanical and unique optical designs make it ideal for illuminating buildings facades, bridges, overpasses and any application that requires a linear lighting solution. Available in white, monochromatic colors, RGB, RGBW and tunable white and DMX control option available with up to 8 pixels (8IDs) to give architects and designers the freedom to explore a wide range of concepts and design with no limitations.

Warnings and Safety

- For outdoor use only

Product data

General Information	
Value ladder	Performance

Mechanical and Housing	
Net Weight (Piece)	1.699 kg

Product Data	
Order product name	ZCP383 L50 glare shield (15 pcs)
Full product name	ZCP383 L50 glare shield (15 pcs)

Full product code	871951494677400
Order code	911401756532
Material Nr. (12NC)	911401756532
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514946774
Numerator - Packs per outer box	1
EAN/UPC - Case	8719514946774

UniStrip G4

Dimensional drawing



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.