



Uni DMX controls and accessories

ZXP399 main controller DMX

Uni DMX controls and accessories, 90 to 264 V, 50 to 60 Hz, IP20 | Finger-protected, Yes, Black

The ZXP399 DMX Controls and Wiring Accessories are to be used with our architectural and facade lighting luminaires (UniFlood C, M and G, UniStrip G4, UniEdge, UniDot G2, UniString and UniBar). DMX Controls include main controller, stand-alone controller, sub-controllers, DMX amplifier and DMX addressing device. Main Controller: Industrial computer that can control up to 6000 DMX universes. Stand-alone Controller: Fits for medium applications with up to 700 DMX universes. Wiring accessories include leader and jumper cables with male and female IP67 connectors and end-caps. Addressing Device: Hand-held device that can write DMX addresses to a whole run on-site within minutes. DMX Amplifier: Compact, IP65 and low power repeater that can amplify the DMX signal for up 100 meters.

Product data

Operating and Electrical	
Input Voltage	90 to 264 V
Line Frequency	50 to 60 Hz
Mechanical and Housing	
Overall length	482 mm
Overall width	361 mm
Overall height	177 mm
Dimensions (Height x Width x Depth)	177 x 361 x 482 mm
Ingress protection code	IP20 [Finger-protected]
Accessory color	Black

Net Weight (Piece)	11.649 kg
Approval and Application	
CE mark	Yes
Product Data	
Order product name	ZXP399 main controller DMX
Full product name	ZXP399 main controller DMX
Full product code	871951494685900
Order code	911401756612
Material Nr. (12NC)	911401756612

Uni DMX controls and accessories

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514946859
Numerator - Packs per outer box	1

EAN/UPC - Case	8719514946859
----------------	---------------

Dimensional drawing

