



# Uni DMX controls and accessories

## ZXP399 main controller DMX

Uni DMX controls and accessories, 90 to 264 V, 50 to 60 Hz, IP20 | Finger-protected, Yes, Black

The ZXP399 DMX Controls and Wiring Accessories are to be used with our architectural and facade lighting luminaires (UniFlood C, M and G, UniStrip G4, UniEdge, UniDot G2, UniString and UniBar). DMX Controls include main controller, stand-alone controller, sub-controllers, DMX amplifier and DMX addressing device. Main Controller: Industrial computer that can control up to 6000 DMX universes. Stand-alone Controller: Fits for medium applications with up to 700 DMX universes. Wiring accessories include leader and jumper cables with male and female IP67 connectors and end-caps. Addressing Device: Hand-held device that can write DMX addresses to a whole run on-site within minutes. DMX Amplifier: Compact, IP65 and low power repeater that can amplify the DMX signal for up to 100 meters.

### Product data

Operating and Electrical		Net Weight (Piece)	
Input Voltage	90 to 264 V		11.649 kg
Line Frequency	50 to 60 Hz	<b>Approval and Application</b>	
<b>Mechanical and Housing</b>		CE mark	Yes
Overall length	482 mm	<b>Product Data</b>	
Overall width	361 mm	Order product name	ZXP399 main controller DMX
Overall height	177 mm	Full product name	ZXP399 main controller DMX
Dimensions (Height x Width x Depth)	177 x 361 x 482 mm	Full product code	871951494685900
Ingress protection code	IP20 [Finger-protected]	Order code	911401756612
Accessory color	Black	Material Nr. (12NC)	911401756612

## Uni DMX controls and accessories

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514946859
Numerator - Packs per outer box	1

EAN/UPC - Case	8719514946859
----------------	---------------

### Dimensional drawing

