



Uni DMX controls and accessories

ZXP399 sub-controller 12V 16port DMX/RDM

Uni DMX controls and accessories, 12 DC V, IP20 | Finger-protected, Yes, Black

The ZXP399 DMX Controls and Wiring Accessories are to be used with our architectural and facade lighting luminaires (UniFlood C, M and G, UniStrip G4, UniEdge, UniDot G2, UniString and UniBar). DMX Controls include a main controller, stand-alone controller, sub-controllers, DMX amplifier and DMX addressing device. Main Controller: Industrial computer that can control up to 6,000 DMX universes. Stand-alone Controller: Fits all medium applications with up to 700 DMX universes. Wiring accessories include leader and jump cables with male and female IP67 connectors and end-caps. Addressing Device: Hand-held device that can write DMX addresses to a whole run on-site within minutes. DMX Amplifier: Compact, IP65 and low-power repeater that can amplify the DMX signal for up 100 metres.

Product data

Operating and Electrical		Net Weight (Piece)	
Input Voltage	12 DC V	2.899 kg	
Line Frequency	- Hz	Approval and Application	
Mechanical and Housing		CE mark	Yes
Overall length	482 mm	Product Data	
Overall width	193 mm	Order product name	ZXP399 sub-controller 12V 16port DMX/RDM
Overall height	66 mm	Full product name	ZXP399 sub-controller 12V 16port DMX/RDM
Dimensions (Height x Width x Depth)	66 x 193 x 482 mm	Full product code	871951494689700
Ingress protection code	IP20 [Finger-protected]	Order code	911401756652
Accessory color	Black	Material Nr. (12NC)	911401756652

Uni DMX controls and accessories

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514946897
Numerator - Packs per outer box	1

EAN/UPC - Case	8719514946897
----------------	---------------

Dimensional drawing

