



UNILinear Flex

BGC401 1150LM 14W 3000K L5 1010 T G

UNILinear Flex, 5750 lm, 56 W, 930 warm white, Safety class III

UNILinear Flex is really and excellently waterproof and anti-dust LED strips with professional design to guarantee lighting performance. Thanks to filling with anti-UV polyurethane and processing by irrigation methods sealing glue, it not only ensure high quality of lighting color consistency but also protect products outdoor against from harsh environments outdoors. It's can be used for decoration lighting and guidance lighting outdoors, the higher CRI (80) delivers good performance of lighting in color rendering.

Product data

General Information		Cable	
Driver included	No	Cable	Cable 0.6 m without plug
Lighting Technology	LED	Protection class IEC	Safety class III
Value ladder	Performance		
Light Technical		Controls and Dimming	
Luminous Flux	5,750 lm	Dimmable	No
Correlated Color Temperature (Nom)	3000 K	Control interface	-
Luminous Efficacy (rated) (Nom)	82 lm/W	Constant light output	No
Color rendering index (CRI)	>90		
Light source color	930 warm white	Mechanical and Housing	
Operating and Electrical		Housing Material	Silicon rubber
Input Voltage	24 DC V	Optical cover material	Silicon rubber
Line Frequency	- Hz	Fixation material	Stainless steel
Power Consumption	56 W	Housing Color	White
Power Factor (Fraction)	1.0	Overall length	10.5 mm
Connection	Flying leads/wires	Overall width	5,000 mm
		Overall height	10 mm
		Dimensions (Height x Width x Depth)	10 x 5000 x 11 mm
		Ingress protection code	IP66 [Dust penetration-protected, jet-proof]

UNILinear Flex

Mech. impact protection code	IK04 [0.5 J standard plus]
Optical cover type	Opal
Net Weight (Piece)	0.760 kg

Approval and Application

CE mark	No
Ambient temperature range	-40 to +45 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	-10%,+15%
Initial chromaticity	4 SDCM
Power consumption tolerance	+/-10%

Product Data

Order product name	BGC401 1150LM 14W 3000K L5 1010 T G
Full product name	BGC401 1150LM 14W 3000K L5 1010 T G
Full product code	692382863728600
Order code	911401767752
Material Nr. (12NC)	911401767752
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828637286
Numerator - Packs per outer box	10
EAN/UPC - Case	6923828637286

Dimensional drawing

