



Uni DMX controls and accessories

ZXP399 samples case 24V DMX

Uni DMX controls and accessories, Aluminum

The ZXP399 DMX Controls and Wiring Accessories are to be used with our architectural and facade lighting luminaires (UniFlood C, M and G, UniStrip G4, UniEdge, UniDot G2, UniString and UniBar). DMX Controls include main controller, stand-alone controller, sub-controllers, DMX amplifier and DMX addressing device. Main Controller: Industrial computer that can control up to 6000 DMX universes. Stand-alone Controller: Fits for medium applications with up to 700 DMX universes. Wiring accessories include leader and jumper cables with male and female IP67 connectors and end-caps. Addressing Device: Hand-held device that can write DMX addresses to a whole run on-site within minutes. DMX Amplifier: Compact, IP65 and low power repeater that can amplify the DMX signal for up 100 meters.

Product data

Operating and Electrical	
Input Voltage	200 to 240 V
Line Frequency	50 to 60 Hz
Protection class IEC	Safety class I
Mechanical and Housing	
Overall length	540 mm
Overall width	390 mm
Overall height	240 mm
Dimensions (Height x Width x Depth)	240 x 390 x 540 mm
Material	Aluminum
Ingress protection code	IP20 [Finger-protected]

Accessory color	Aluminum
Net Weight (Piece)	14.000 kg
Approval and Application	
CE mark	No
Product Data	
Order product name	ZXP399 samples case 24V DMX
Full product name	ZXP399 samples case 24V DMX
Full product code	872016972504100
Order code	911401772862
Material Nr. (12NC)	911401772862

Uni DMX controls and accessories

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169725041
Numerator - Packs per outer box	1

EAN/UPC - Case	8720169725041
----------------	---------------

Dimensional drawing

