



# ZXP399 DMX Controls and Accessories

## ZXP399 samples case 24V DMX

### ZXP399 DMX Controls and Accessories, Aluminium

The ZXP399 DMX Controls and Wiring Accessories are to be used with our architectural and facade lighting luminaires (UniFlood C, M and G, UniStrip G4, UniEdge, UniDot G2, UniString and UniBar). DMX Controls include a main controller, stand-alone controller, sub-controllers, DMX amplifier and DMX addressing device. Main Controller: Industrial computer that can control up to 6,000 DMX universes. Stand-alone Controller: Fits all medium applications with up to 700 DMX universes. Wiring accessories include leader and jump cables with male and female IP67 connectors and end-caps. Addressing Device: Hand-held device that can write DMX addresses to a whole run on-site within minutes. DMX Amplifier: Compact, IP65 and low-power repeater that can amplify the DMX signal for up to 100 metres.

### Product data

Operating and Electrical		Material	
Input Voltage	200 to 240 V		Aluminium
Line Frequency	50 to 60 Hz	Ingress protection code	IP20 [Finger-protected]
Protection class IEC	Safety class I	Accessory colour	Aluminium
		Net Weight (Piece)	14.000 kg
Mechanical and Housing		Approval and Application	
Overall length	540 mm	CE mark	No
Overall width	390 mm		
Overall height	240 mm	Product Data	
Dimensions (height x width x depth)	240 x 390 x 540 mm	Order product name	ZXP399 samples case 24V DMX

## ZXP399 DMX Controls and Accessories

Full product name	ZXP399 samples case 24V DMX
Full EOC	872016972504100
Order code	911401772862
Material no. (12 NC)	911401772862
Numerator – quantity per pack	1

EAN/UPC – Product/Case	8720169725041
Numerator – packs per outer box	1
EAN/UPC – Case	8720169725041

### Dimensional drawing

