



# Uni DMX controls and accessories

## ZXP399 samples case 24V DMX

Uni DMX controls and accessories, Aluminum

The ZXP399 DMX Controls and Wiring Accessories are to be used with our architectural and facade lighting luminaires (UniFlood C, M and G, UniStrip G4, UniEdge, UniDot G2, UniString and UniBar). DMX Controls include main controller, stand-alone controller, sub-controllers, DMX amplifier and DMX addressing device. Main Controller: Industrial computer that can control up to 6000 DMX universes. Stand-alone Controller: Fits for medium applications with up to 700 DMX universes. Wiring accessories include leader and jumper cables with male and female IP67 connectors and end-caps. Addressing Device: Hand-held device that can write DMX addresses to a whole run on-site within minutes. DMX Amplifier: Compact, IP65 and low power repeater that can amplify the DMX signal for up 100 meters.

### Product data

Operating and Electrical		Accessory color	
Input Voltage	200 to 240 V	Aluminum	
Line Frequency	50 to 60 Hz	Net Weight (Piece)	
Protection class IEC	Safety class I	14.000 kg	
Mechanical and Housing		Approval and Application	
Overall length	540 mm	CE mark	
Overall width	390 mm	No	
Overall height	240 mm	Product Data	
Dimensions (Height x Width x Depth)	240 x 390 x 540 mm	Order product name	ZXP399 samples case 24V DMX
Material	Aluminum	Full product name	ZXP399 samples case 24V DMX
Ingress protection code	IP20 [Finger-protected]	Full product code	872016972504100
		Order code	911401772862
		Material Nr. (12NC)	911401772862

## Uni DMX controls and accessories

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169725041
Numerator - Packs per outer box	1

EAN/UPC - Case	8720169725041
----------------	---------------

### Dimensional drawing

