# UniFlood C Pro

## BVP374 60LED RGBWW 220V 45 DMX 150W HP

UniFlood C Pro, 5650 lm, 150 W, RGBW, Dynamic DMX/RDM, Safety class I

Philips UniFlood C Pro offers a unique rugged elegance, with a cylindrical form and flowing lines that connect the front and back housings beautifully. This is compact architectural floodlighting design where every element has a purpose; the front section provides exceptional lighting, while the back section houses all the electrical components. Between the two, the fins dissipate heat and also serve as a decorative element. Exterior-rated, Philips UniFlood C Pro is a cost-effective, architectural LED floodlight that is designed for façade, landscape and outdoor floodlighting applications. The robust mechanical design and high-efficiency optics make it ideal for illuminating multi-story exterior façades, bridges, landmarks and monuments. Architects and designers have the freedom to explore a wide range of concepts and designs with no limitations, thanks to a range of colors, multiple spread lenses and a DMX512/RDM control option.

### Warnings and Safety

- For outdoor use only

### Product data

| General Information | |
|---|---|
| **Color Code** | RGBW |
| **Driver included** | Yes |
| **Lighting Technology** | LED |
| **Value ladder** | Performance |

| Light Technical | |
|---|---|
| **Luminous Flux** | 5,650 lm |
| **Correlated Color Temperature (Nom)** | - |
| **Luminous Efficacy (rated) (Nom)** | 38 lm/W |
| **Color rendering index (CRI)** | N.A. |
| **Light source color** | RGBW |

| Operating and Electrical | |
|---|---|
| **Input Voltage** | 220 to 240 V |
| **Line Frequency** | 50 to 60 Hz |
| **Power Consumption** | 150 W |
| **Power Factor (Fraction)** | 0.9 |

# UniFlood C Pro

| | |
|---|---|
| **Connection** | Flying leads/wires and 2 Push-in connector 4-pole |
| **Cable** | Cable 0.5 m without plug 3-pole and 2 Cables 0.5 m with connector 4-pole |
| **Protection class IEC** | Safety class I |

| Controls and Dimming | |
|---|---|
| **Dimmable** | Yes |
| **Control interface** | Dynamic DMX/RDM |

| Mechanical and Housing | |
|---|---|
| **Housing Material** | Aluminum die cast |
| **Optical cover material** | Polycarbonate |
| **Housing Color** | Dark gray |
| **Ingress protection code** | IP66 [Dust penetration-protected, jet-proof] |
| **Mech. impact protection code** | IK06 [1 J] |
| **Optical cover type** | Clear glass |
| **Net Weight (Piece)** | 8.000 kg |

| Approval and Application | |
|---|---|
| **CE mark** | Yes |

| | |
|---|---|
| **Ambient temperature range** | -40 to +50 °C |

| Initial Performance (IEC Compliant) | |
|---|---|
| **Luminous flux tolerance** | +/-10% |
| **Power consumption tolerance** | +/-10% |

| Product Data | |
|---|---|
| **Order product name** | BVP374 60LED RGBWW 220V 45 DMX 150W HP |
| **Full product name** | BVP374 60LED RGBWW 220V 45 DMX 150W HP |
| **Full product code** | 872016950655899 |
| **Order code** | 911401776733 |
| **Material Nr. (12NC)** | 911401776733 |
| **Numerator - Quantity Per Pack** | 1 |
| **EAN/UPC - Product/Case** | 8720169506558 |
| **Numerator - Packs per outer box** | 2 |
| **EAN/UPC - Case** | 8720169506558 |

## Dimensional drawing



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.