

## BN126Z SC

911401776802



## CoreLine Batten, Accessory, IP20 | Finger-protected, IK04 | 0.5 J standard plus, Steel

The CoreLine Batten delivers on the CoreLine promise of innovative, easy-to-use and high-quality luminaires. The efficient design makes installation quick and easy, enabling seamless light-line creation without additional accessories. CoreLine Batten provides universal light distribution, supporting homogeneous illuminance and visual comfort. Interact Ready luminaires with integrated wireless communications are also available, for use with Interact gateways, sensors and software.

### Warnings and Safety

- The product is IPX0 & as such is not protected against water ingress & as such we strongly recommend that the environment in which the luminaire is to be installed is suitably checked
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure & product warranty will become void

## General Information

|              |             |
|--------------|-------------|
| Value ladder | Performance |
|--------------|-------------|

## Operating and Electrical

|                      |                |
|----------------------|----------------|
| Input Voltage        | - V            |
| Line Frequency       | - Hz           |
| Protection class IEC | Safety class I |

## Mechanical and Housing

|                                     |                            |
|-------------------------------------|----------------------------|
| Overall length                      | 57 mm                      |
| Overall width                       | 22 mm                      |
| Overall height                      | 1,000 mm                   |
| Dimensions (Height x Width x Depth) | 1000 x 22 x 57 mm          |
| Material                            | Steel                      |
| Ingress protection code             | IP20 [Finger-protected]    |
| Mech. impact protection code        | IK04 [0.5 J standard plus] |
| Accessory color                     | Steel                      |
| Net Weight (Piece)                  | 0.064 kg                   |

## Approval and Application

|                   |     |
|-------------------|-----|
| CE mark           | Yes |
| EU RoHS compliant | Yes |

## Related Documents

| Documents and certificates | Document Name                                                | Download                                                                                                       |
|----------------------------|--------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------|
| Installation Instructions  | BN126C-Mounting Instruction-EUR-V1,0-2019-12-19-FINAL v2.pdf | <a href="#">Download</a>  |
| Tender text                | Tender_Text_911401776802_en_NZ.txt                           | <a href="#">Download</a>  |

## Sustainability Data

|                                            |                                |
|--------------------------------------------|--------------------------------|
| Non-virgin material ratio of the packaging | Cardboard > 80% recycled       |
| Packaging Recyclable content ratio         | Cardboard recycling rate > 80% |
| Packaging Material                         | Cardboard                      |

## Product Data

|                                 |                 |
|---------------------------------|-----------------|
| Order product name              | BN126Z SC       |
| Full product name               | BN126Z SC       |
| Full product code               | 871016336574999 |
| Order code                      | 911401776802    |
| Material Nr. (12NC)             | 911401776802    |
| Numerator - Quantity Per Pack   | 1               |
| EAN/UPC - Product/Case          | 8710163365749   |
| Numerator - Packs per outer box | 108             |
| EAN/UPC - Case                  | 8710163365831   |

