



CoreLine Batten

BN126Z SC

CoreLine Batten, Accessory, IP20 | Finger-protected, IK04 | 0.5 J standard plus, Steel

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Batten range of LED products can be used to replace traditional battens with fluorescent lamps. The process of selecting, installing and maintaining is so easy – it’s a simple switch.

Warnings and Safety

- The product is IPX0 & as such is not protected against water ingress & as such we strongly recommend that the environment in which the luminaire is to be installed is suitably checked
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure & product warranty will become void

Product data

General Information		Dimensions (Height x Width x Depth)	1000 x 22 x 57 mm
Value ladder	Performance	Material	Steel
Operating and Electrical		Ingress protection code	IP20 [Finger-protected]
Input Voltage	- V	Mech. impact protection code	IK04 [0.5 J standard plus]
Line Frequency	- Hz	Accessory color	Steel
Protection class IEC	Safety class I	Net Weight (Piece)	0.064 kg
Mechanical and Housing		Approval and Application	
Overall length	57 mm	CE mark	Yes
Overall width	22 mm	EU RoHS compliant	Yes
Overall height	1,000 mm		

CoreLine Batten

Sustainability Data

Non-virgin material ratio of the packaging Cardboard > 80% recycled Plastic >35% recycled

Packaging Recyclable content ratio Cardboard recycling rate > 80% Plastic recycling rate > 40%

Packaging Material Cardboard Plastic

Product Data

Order product name BN126Z SC

Full product name BN126Z SC

Full product code 871016336574999

Order code 911401776802

Material Nr. (12NC) 911401776802

Numerator - Quantity Per Pack 1

EAN/UPC - Product/Case 8710163365749

Numerator - Packs per outer box 108

EAN/UPC - Case 8710163365831

