



UniBar

BCS341 60LED 27K 24V OC L100 10PX

UniBar, 725 lm, 15 W, Warm white, Dynamic DMX, Safety class III

UniBar is a surface mounted, exterior-rated and slim sized linear LED direct view luminaire that is designed for façade and outdoor architectural lighting applications. The robust mechanical and unique optical design make it ideal for buildings facades, media facades, bridges, overpasses and any application that requires a slim linear direct view lighting solution. Direct view spread lens, through wiring for end-to-end connection and DMX control option available with up to 10 pixels (10IDs) to give architects and designers the freedom to explore a wide range of concepts and design with no limitations. Available in white, monochromatic colors, RGB, RGBW and tunable white.

Product data

General Information	
Driver included	No
Lighting Technology	LED
Light Technical	
Luminous Flux	725 lm
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	48 lm/W
Color rendering index (CRI)	80
Light source color	Warm white
Operating and Electrical	
Input Voltage	24 DC V
Line Frequency	- Hz
Power Consumption	15 W
Power Factor (Fraction)	0.9

Connection	2 Push-in connector 5-pole
Cable	2 cables (0.2m input + 0.1m output) with connectors 5-pole
Protection class IEC	Safety class III
Controls and Dimming	
Dimmable	Yes
Control interface	Dynamic DMX
Mechanical and Housing	
Housing Material	Aluminum extruded
Optical cover material	Polycarbonate
Housing Color	Silver
Overall length	1,000 mm
Overall width	35 mm
Overall height	65 mm

UniBar

Dimensions (Height x Width x Depth)	65 x 35 x 1000 mm
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Optical cover type	Opal
Net Weight (Piece)	0.886 kg
Approval and Application	
CE mark	Yes
Ambient temperature range	-40 to +50 °C
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data	
Order product name	BCS341 60LED 27K 24V OC L100 10PX
Full product name	BCS341 60LED 27K 24V OC L100 10PX
Full product code	871951494714699
Order code	911401779102
Material Nr. (12NC)	911401779102
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514947146
Numerator - Packs per outer box	24
EAN/UPC - Case	8719514947146

Dimensional drawing

