



# UniBar

## BCS341 60LED 30K 24V OC L100

UniBar, 725 lm, 15 W, Warm white, Safety class III

UniBar is a surface mounted, exterior-rated and slim sized linear LED direct view luminaire that is designed for façade and outdoor architectural lighting applications. The robust mechanical and unique optical design make it ideal for buildings facades, media facades, bridges, overpasses and any application that requires a slim linear direct view lighting solution. Direct view spread lens, through wiring for end-to-end connection and DMX control option available with up to 10 pixels (10IDs) to give architects and designers the freedom to explore a wide range of concepts and design with no limitations. Available in white, monochromatic colors, RGB, RGBW and tunable white.

### Product data

General Information		Connection	
Driver included	No	Cable	2 cables (0.2m input + 0.1m output) with connectors 2-pole
Lighting Technology	LED	Protection class IEC	Safety class III
Light Technical		Controls and Dimming	
Luminous Flux	725 lm	Dimmable	No
Correlated Color Temperature (Nom)	3000 K	Control interface	-
Luminous Efficacy (rated) (Nom)	48 lm/W	Mechanical and Housing	
Color rendering index (CRI)	80	Housing Material	Aluminum extruded
Light source color	Warm white	Optical cover material	Polycarbonate
Operating and Electrical		Housing Color	Silver
Input Voltage	24 DC V	Overall length	1,000 mm
Line Frequency	- Hz	Overall width	35 mm
Power Consumption	15 W	Overall height	65 mm
Power Factor (Fraction)	0.9		

# UniBar

<b>Dimensions (Height x Width x Depth)</b>	65 x 35 x 1000 mm
<b>Ingress protection code</b>	IP66 [Dust penetration-protected, jet-proof]
<b>Mech. impact protection code</b>	IK08 [5 J vandal-protected]
<b>Optical cover type</b>	Opal
<b>Net Weight (Piece)</b>	0.886 kg
<b>Approval and Application</b>	
<b>CE mark</b>	Yes
<b>Ambient temperature range</b>	-40 to +50 °C
<b>Initial Performance (IEC Compliant)</b>	
<b>Luminous flux tolerance</b>	+/-10%
<b>Power consumption tolerance</b>	+/-10%

<b>Product Data</b>	
<b>Order product name</b>	BCS341 60LED 30K 24V OC L100
<b>Full product name</b>	BCS341 60LED 30K 24V OC L100
<b>Full product code</b>	872016972534899
<b>Order code</b>	911401779132
<b>Material Nr. (12NC)</b>	911401779132
<b>Numerator - Quantity Per Pack</b>	1
<b>EAN/UPC - Product/Case</b>	8720169725348
<b>Numerator - Packs per outer box</b>	24
<b>EAN/UPC - Case</b>	8720169725348

## Dimensional drawing

