



# UniStrip G4

## BCP386 12LED 27K 24V 60 L30

UniStrip G4, 200 lm, 3 W, Warm white, Safety class III

UniStrip G4 is a surface mounted, exterior-rated LED luminaire that is designed for façade and outdoor architectural lighting applications. One family that fits all your needs, wall washing, grazing and also linear flood lighting. The robust mechanical and unique optical designs make it ideal for illuminating buildings facades, bridges, overpasses and any application that requires a linear lighting solution. Available in white, monochromatic colors, RGB, RGBW and tunable white and DMX control option available with up to 8 pixels (8IDs) to give architects and designers the freedom to explore a wide range of concepts and design with no limitations.

### Warnings and Safety

- For outdoor use only

### Product data

| General Information                |             | Line Frequency          |                                       |
|------------------------------------|-------------|-------------------------|---------------------------------------|
| Driver included                    | No          | Line Frequency          | - Hz                                  |
| Lighting Technology                | LED         | Power Consumption       | 3 W                                   |
| Value ladder                       | Performance | Power Factor (Fraction) | 1                                     |
| Light Technical                    |             | Connection              | 2 Push-in connector 2-pole            |
| Luminous Flux                      | 200 lm      | Cable                   | 2 cables 0.15m with connectors 2-pole |
| Correlated Color Temperature (Nom) | 2700 K      | Protection class IEC    | Safety class III                      |
| Luminous Efficacy (rated) (Nom)    | 67 lm/W     | Controls and Dimming    |                                       |
| Color rendering index (CRI)        | 80          | Dimmable                | No                                    |
| Light source color                 | Warm white  | Control interface       | -                                     |
| Operating and Electrical           |             | Mechanical and Housing  |                                       |
| Input Voltage                      | 24 DC V     | Housing Material        | Aluminum extruded                     |
|                                    |             | Optical cover material  | Polymethyl methacrylate               |

## UniStrip G4

|                                     |  |
|-------------------------------------|--|
| Housing Color                       | Dark gray                                    |
| Overall length                      | 300 mm                                       |
| Overall width                       | 25.4 mm                                      |
| Overall height                      | 71.6 mm                                      |
| Dimensions (Height x Width x Depth) | 72 x 25 x 300 mm                             |
| Ingress protection code             | IP66 [Dust penetration-protected, jet-proof] |
| Mech. impact protection code        | IK06 [I J]                                   |
| Optical cover type                  | Clear glass                                  |
| Net Weight (Piece)                  | 0.360 kg                                     |

### Approval and Application

|                           |               |
|---------------------------|---------------|
| CE mark                   | Yes           |
| Ambient temperature range | -40 to +50 °C |

### Initial Performance (IEC Compliant)

|                         |        |
|-------------------------|--------|
| Luminous flux tolerance | +/-10% |
|-------------------------|--------|

|                             |        |
|-----------------------------|--------|
| Power consumption tolerance | +/-10% |
|-----------------------------|--------|

### Product Data

|                                 |                             |
|---------------------------------|-----------------------------|
| Order product name              | BCP386 12LED 27K 24V 60 L30 |
| Full product name               | BCP386 12LED 27K 24V 60 L30 |
| Full product code               | 871951451363199             |
| Order code                      | 911401779982                |
| Material Nr. (12NC)             | 911401779982                |
| Numerator - Quantity Per Pack   | 1                           |
| EAN/UPC - Product/Case          | 8719514513631               |
| Numerator - Packs per outer box | 50                          |
| EAN/UPC - Case                  | 8719514513631               |

## Dimensional drawing

