



# UniStrip G4

BCP386 30LED 27K 24V 60 L50

UniStrip G4, 495 lm, 7.5 W, Warm white, Safety class III

UniStrip G4 is a surface mounted, exterior-rated LED luminaire that is designed for façade and outdoor architectural lighting applications. One family that fits all your needs, wall washing, grazing and also linear flood lighting. The robust mechanical and unique optical designs make it ideal for illuminating buildings facades, bridges, overpasses and any application that requires a linear lighting solution. Available in white, monochromatic colors, RGB, RGBW and tunable white and DMX control option available with up to 8 pixels (8IDs) to give architects and designers the freedom to explore a wide range of concepts and design with no limitations.

## Warnings and Safety

- For outdoor use only

## Product data

| General Information                |             |
|------------------------------------|-------------|
| Driver included                    | No          |
| Lighting Technology                | LED         |
| Value ladder                       | Performance |
| Light Technical                    |             |
| Luminous Flux                      | 495 lm      |
| Correlated Color Temperature (Nom) | 2700 K      |
| Luminous Efficacy (rated) (Nom)    | 66 lm/W     |
| Color rendering index (CRI)        | 80          |
| Light source color                 | Warm white  |
| Operating and Electrical           |             |
| Input Voltage                      | 24 DC V     |

| Line Frequency          | - Hz                                  |
|-------------------------|---------------------------------------|
| Power Consumption       | 7.5 W                                 |
| Power Factor (Fraction) | 1                                     |
| Connection              | 2 Push-in connector 2-pole            |
| Cable                   | 2 cables 0.15m with connectors 2-pole |
| Protection class IEC    | Safety class III                      |
| Controls and Dimming    |                                       |
| Dimmable                | No                                    |
| Control interface       | -                                     |
| Mechanical and Housing  |                                       |
| Housing Material        | Aluminum extruded                     |
| Optical cover material  | Polymethyl methacrylate               |

UniStrip G4

|                                     |                                              |
|-------------------------------------|----------------------------------------------|
| Housing Color                       | Dark gray                                    |
| Overall length                      | 500 mm                                       |
| Overall width                       | 25.4 mm                                      |
| Overall height                      | 71.6 mm                                      |
| Dimensions (Height x Width x Depth) | 72 x 25 x 500 mm                             |
| Ingress protection code             | IP66 [Dust penetration-protected, jet-proof] |
| Mech. impact protection code        | IK06 [1 J]                                   |
| Optical cover type                  | Clear glass                                  |
| Net Weight (Piece)                  | 0.456 kg                                     |

Approval and Application

|                           |               |
|---------------------------|---------------|
| CE mark                   | Yes           |
| Ambient temperature range | -40 to +50 °C |

Initial Performance (IEC Compliant)

|                         |        |
|-------------------------|--------|
| Luminous flux tolerance | +/-10% |
|-------------------------|--------|

|                             |        |
|-----------------------------|--------|
| Power consumption tolerance | +/-10% |
|-----------------------------|--------|

Product Data

|                                 |                             |
|---------------------------------|-----------------------------|
| Order product name              | BCP386 30LED 27K 24V 60 L50 |
| Full product name               | BCP386 30LED 27K 24V 60 L50 |
| Full product code               | 871951451388499             |
| Order code                      | 911401780232                |
| Material Nr. (12NC)             | 911401780232                |
| Numerator - Quantity Per Pack   | 1                           |
| EAN/UPC - Product/Case          | 8719514513884               |
| Numerator - Packs per outer box | 50                          |
| EAN/UPC - Case                  | 8719514513884               |

Dimensional drawing

