



# UniStrip G4

## BCP386 60LED 30K 24V 45 L100

UniStrip G4, 975 lm, 15 W, Warm white, Safety class III

UniStrip G4 is a surface mounted, exterior-rated LED luminaire that is designed for façade and outdoor architectural lighting applications. One family that fits all your needs, wall washing, grazing and also linear flood lighting. The robust mechanical and unique optical designs make it ideal for illuminating buildings facades, bridges, overpasses and any application that requires a linear lighting solution. Available in white, monochromatic colors, RGB, RGBW and tunable white and DMX control option available with up to 8 pixels (8IDs) to give architects and designers the freedom to explore a wide range of concepts and design with no limitations.

### Warnings and Safety

- For outdoor use only

### Product data

General Information		Line Frequency	
Driver included	No	Line Frequency	- Hz
Lighting Technology	LED	Power Consumption	15 W
Value ladder	Performance	Power Factor (Fraction)	1
Light Technical		Connection	2 Push-in connector 2-pole
Luminous Flux	975 lm	Cable	2 cables 0.15m with connectors 2-pole
Correlated Color Temperature (Nom)	3000 K	Protection class IEC	Safety class III
Luminous Efficacy (rated) (Nom)	65 lm/W	Controls and Dimming	
Color rendering index (CRI)	80	Dimmable	No
Light source color	Warm white	Control interface	-
Operating and Electrical		Mechanical and Housing	
Input Voltage	24 DC V	Housing Material	Aluminum extruded
		Optical cover material	Polymethyl methacrylate

## UniStrip G4

Housing Color	Dark gray
Overall length	1,000 mm
Overall width	25.4 mm
Overall height	71.6 mm
Dimensions (Height x Width x Depth)	72 x 25 x 1000 mm
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Optical cover type	Clear glass
Net Weight (Piece)	0.908 kg

### Approval and Application

CE mark	Yes
Ambient temperature range	-40 to +50 °C

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Power consumption tolerance	+/-10%
-----------------------------	--------

### Product Data

Order product name	BCP386 60LED 30K 24V 45 L100
Full product name	BCP386 60LED 30K 24V 45 L100
Full product code	871951451409699
Order code	911401780442
Material Nr. (12NC)	911401780442
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514514096
Numerator - Packs per outer box	25
EAN/UPC - Case	8719514514096

## Dimensional drawing

