



UniStrip G4

BCP386 60LED 30K 24V A11 L100

UniStrip G4, 960 lm, 15 W, Warm white, Safety class III

UniStrip G4 is a surface mounted, exterior-rated LED luminaire that is designed for façade and outdoor architectural lighting applications. One family that fits all your needs, wall washing, grazing and also linear flood lighting. The robust mechanical and unique optical designs make it ideal for illuminating buildings facades, bridges, overpasses and any application that requires a linear lighting solution. Available in white, monochromatic colors, RGB, RGBW and tunable white and DMX control option available with up to 8 pixels (8IDs) to give architects and designers the freedom to explore a wide range of concepts and design with no limitations.

Warnings and Safety

- For outdoor use only

Product data

General Information	
Driver included	No
Lighting Technology	LED
Value ladder	Performance

Light Technical	
Luminous Flux	960 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	64 lm/W
Color rendering index (CRI)	80
Light source color	Warm white

Operating and Electrical	
Input Voltage	24 DC V

Line Frequency	- Hz
Power Consumption	15 W
Power Factor (Fraction)	1
Connection	2 Push-in connector 2-pole
Cable	2 cables 0.15m with connectors 2-pole
Protection class IEC	Safety class III

Controls and Dimming	
Dimmable	No
Control interface	-

Mechanical and Housing	
Housing Material	Aluminum extruded
Optical cover material	Polymethyl methacrylate

UniStrip G4

Housing Color	Dark gray
Overall length	1,000 mm
Overall width	25.4 mm
Overall height	71.6 mm
Dimensions (Height x Width x Depth)	72 x 25 x 1000 mm
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Optical cover type	Clear glass
Net Weight (Piece)	0.908 kg

Approval and Application

CE mark	Yes
Ambient temperature range	-40 to +50 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Power consumption tolerance	+/-10%
-----------------------------	--------

Product Data	
Order product name	BCP386 60LED 30K 24V A11 L100
Full product name	BCP386 60LED 30K 24V A11 L100
Full product code	871951451421899
Order code	911401780562
Material Nr. (12NC)	911401780562
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514514218
Numerator - Packs per outer box	25
EAN/UPC - Case	8719514514218

Dimensional drawing

