



UniStrip G4

BCP386 60LED RGBNW 24V 45 L100 DMX

UniStrip G4, 750 lm, 15 W, Red, green, blue and white, Dynamic DMX, Safety class III

UniStrip G4 is a surface mounted, exterior-rated LED luminaire that is designed for façade and outdoor architectural lighting applications. One family that fits all your needs, wall washing, grazing and also linear flood lighting. The robust mechanical and unique optical designs make it ideal for illuminating buildings facades, bridges, overpasses and any application that requires a linear lighting solution. Available in white, monochromatic colors, RGB, RGBW and tunable white and DMX control option available with up to 8 pixels (8IDs) to give architects and designers the freedom to explore a wide range of concepts and design with no limitations.

Warnings and Safety

- For outdoor use only

Product data

General Information		Operating and Electrical	
Driver included	No	Input Voltage	24 DC V
Lighting Technology	LED	Line Frequency	- Hz
Value ladder	Performance	Power Consumption	15 W
		Power Factor (Fraction)	1
		Connection	2 Push-in connector 5-pole
		Cable	2 cables 0.15m with connectors 5-pole
		Protection class IEC	Safety class III
Light Technical		Controls and Dimming	
Luminous Flux	750 lm	Dimmable	Yes
Correlated Color Temperature (Nom)	-		
Luminous Efficacy (rated) (Nom)	50 lm/W		
Color rendering index (CRI)	-		
Light source color	Red, green, blue and white		

UniStrip G4

Control interface	Dynamic DMX
Mechanical and Housing	
Housing Material	Aluminum extruded
Optical cover material	Polymethyl methacrylate
Housing Color	Dark gray
Overall length	1,000 mm
Overall width	25.4 mm
Overall height	71.6 mm
Dimensions (Height x Width x Depth)	72 x 25 x 1000 mm
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Optical cover type	Clear glass
Net Weight (Piece)	0.908 kg
Approval and Application	
CE mark	Yes
Ambient temperature range	-40 to +50 °C

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%
Product Data	
Order product name	BCP386 60LED RGBNW 24V 45 L100 DMX
Full product name	BCP386 60LED RGBNW 24V 45 L100 DMX
Full product code	871951451425699
Order code	911401780602
Material Nr. (12NC)	911401780602
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514514256
Numerator - Packs per outer box	25
EAN/UPC - Case	8719514514256

Dimensional drawing

