



Smartbright Waterproof WT065C

WT065C LED68S/840 PSU L1500

Smartbright Waterproof WT065C, 53 W, 6800 lm, 4000 K

The Smartbright Waterproof WT065C range provides maximum performance and durability at great value. As an off-the-shelf LED luminaire solution for all your everyday needs, it can be deployed in a wide variety of locations.

Product data

General Information		Protection class IEC	
Light source engine type	LED	Protection class IEC	Safety class I
Value ladder	Value	Controls and Dimming	
Light Technical		Dimmable	No
Luminous Flux	6,800 lm	Control interface	-
Correlated Color Temperature (Nom)	4000 K	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	125 lm/W	Housing Material	Polycarbonate
Color rendering index (CRI)	>80	Optical cover material	Polycarbonate
Light source color	840 neutral white	Housing Color	Gray and white
Operating and Electrical		Optical cover finish	Opal
Input Voltage	220 to 240 V	Overall length	1,507 mm
Line Frequency	50 or 60 Hz	Overall width	71 mm
Inrush current	6.9 A	Overall height	74 mm
Power Consumption	53 W	Dimensions (Height x Width x Depth)	74 x 71 x 1507 mm
Power Factor (Fraction)	0.9	Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Number of products on MCB of 16 A type B	30	Mech. impact protection code	-
		Optical cover type	Polycarbonate

Smartbright Waterproof WT065C

Net Weight (Piece)	1.620 kg
--------------------	----------

Approval and Application

Flammability mark	For mounting on normally flammable surfaces
CE mark	No
Ambient temperature range	-20 to +40 °C


Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38,0.38) SDCM≤6
Power consumption tolerance	+/-10%

Product Data

Order product name	WT065C LED68S/840 PSU L1500
Full product name	WT065C LED68S/840 PSU L1500
Full product code	692382865543399
Order code	911401800384
Material Nr. (12NC)	911401800384
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828655433
Numerator - Packs per outer box	9
EAN/UPC - Case	6923828655518

Dimensional drawing



WT065C L1500

