



Smartbright Waterproof WT065C

WT065C LED24S/865 PSU L1200

Smartbright Waterproof WT065C, 22 W, 2400 lm, 6500 K

The Smartbright Waterproof WT065C range provides maximum performance and durability at great value. As an off-the-shelf LED luminaire solution for all your everyday needs, it can be deployed in a wide variety of locations.

Product data

General Information		Protection class IEC	Safety class I
Light source engine type	LED	Controls and Dimming	
Value ladder	Value	Dimmable	No
Light Technical		Control interface	-
Luminous Flux	2,400 lm	Mechanical and Housing	
Correlated Color Temperature (Nom)	6500 K	Housing Material	Polycarbonate
Luminous Efficacy (rated) (Nom)	110 lm/W	Optical cover material	Polycarbonate
Color rendering index (CRI)	>80	Housing Color	Gray and white
Light source color	865 cool daylight	Optical cover finish	Opal
Operating and Electrical		Overall length	1,207 mm
Input Voltage	220 to 240 V	Overall width	71 mm
Line Frequency	50 or 60 Hz	Overall height	74 mm
Inrush current	5.16 A	Dimensions (Height x Width x Depth)	74 x 71 x 1207 mm
Power Consumption	22 W	Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Power Factor (Fraction)	0.9	Mech. impact protection code	-
Number of products on MCB of 16 A type B	60	Optical cover type	Polycarbonate

Smartbright Waterproof WT065C

Net Weight (Piece)	1.240 kg
--------------------	----------

Approval and Application

Flammability mark	For mounting on normally flammable surfaces
CE mark	No
Ambient temperature range	-20 to +40 °C


Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.31,0.34) SDCM≤6
Power consumption tolerance	+/-10%

Product Data

Order product name	WT065C LED24S/865 PSU L1200
Full product name	WT065C LED24S/865 PSU L1200
Full product code	692382865544099
Order code	911401800484
Material Nr. (12NC)	911401800484
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828655440
Numerator - Packs per outer box	9
EAN/UPC - Case	6923828655525

Dimensional drawing



WT065C L1200

