



# SmartBright Downlight DN058 WV

## DN058C LED9/865 110-240V L150 SQ

SmartBright Downlight DN058 WV, 7.8 W, 900 lm, 6500 K,  
Symmetric 110°, Matte, IP20 | Finger-protected

SmartBright downlight DN058 WV series products offer reliable lighting performance with long lifetime and meet all the IEC safety regulation requirements. Products have multiple installation, including both recessed and surface mount. Products also have Different shapes as options, round and square shape can meet different customer's requirement. Products have three CCT options with different cut out solutions. Products have no harm to eyes and give eye comfortable experience.

### Product data

General Information	
Number of gear units	1 unit
Gear	EB [Electronic]
Driver included	Yes
Light source engine type	LED
Value ladder	Value
Warranty period	1 years

Light Technical	
Luminous Flux	900 lm
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	115 lm/W
Color rendering index (CRI)	>80
Number of light sources	1
Beam angle of light source	110 degree(s)

Light source color	865 cool daylight
Optic type	Symmetric 110°
Luminaire light beam spread	110°
Unified glare rating CEN	30
Effective projected area	0.75 m <sup>2</sup>

Operating and Electrical	
Input Voltage	110 to 240 V
Line Frequency	50 or 60 Hz
Inrush current	15.2 A
Inrush time	0.084 ms
Power Consumption	7.8 W
Power Factor (Fraction)	0.5
Connection	Flying leads/wires
Cable	2×0.75mm <sup>2</sup> Cable without plug 2-pole

# SmartBright Downlight DN058 WV

Number of products on MCB of 16 A type B	88
Suitable for random switching	No
Protection class IEC	Safety class II

## Controls and Dimming

Dimmable	No
Control interface	-
Maximum dim level	Not applicable

## Mechanical and Housing

Housing Material	Polypropylene
Reflector material	-
Optic material	Polystyrene
Optical cover material	Polystyrene
Housing Color	White RAL 9003
Mounting device	Mounting bracket
Optical cover finish	Matte
Overall length	165 mm
Overall width	165 mm
Overall height	35 mm
Dimensions (Height x Width x Depth)	35 x 165 x 165 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Optical cover type	PS
Net Weight (Piece)	0.190 kg

## Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
----------------	-----------------------------------

Flammability mark	For mounting on normally flammable surfaces
CE mark	No
ENEC mark	-
Photobiological risk	Photobiological risk group 0 @200mm to EN62778
Photobiological risk specification	0.2 m
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	-20 °C to 40 °C


## Initial Performance (IEC Compliant)

Luminous flux tolerance	-10%,+15%
Initial chromaticity	(0.31,0.33) SDCM≤6
Power consumption tolerance	+/-10%

## Product Data

Order product name	DN058C LED9/865 110-240V L150 SQ
Full product name	DN058C LED9/865 110-240V L150 SQ
Full product code	872110331823799
Order code	911401802088
Material Nr. (12NC)	911401802088
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8721103318237
Numerator - Packs per outer box	20
EAN/UPC - Case	8721103319104

## Dimensional drawing



## SmartBright Downlight DN058 WV

