



Ledinaire Waterproof Tube Housing

WT050C 2xTLED L1200

Ledinaire Waterproof Tube Housing, L1200 mm, IP65, IK08

L1200 mm, IP65 | Dust penetration-protected, jet-proof, IK08 | 5 J vandal-protected, Safety class II

Product data

General Information		Accessories	
Value ladder	Value	Accessory color	Gray
		Angle	-
		Net Weight (Piece)	0.800 kg
Light Technical		Approval and Application	
Color rendering index (CRI)	-	CE mark	Yes
Luminaire light beam spread	-	EU RoHS compliant	Yes
Operating and Electrical		Sustainability Data	
Input Voltage	220 to 240 V	Non-virgin material ratio of the packaging	Cardboard > 80% recycled Plastic >35% recycled
Line Frequency	50 or 60 Hz	Packaging Recyclable content ratio	Cardboard recycling rate > 80% Plastic recycling rate > 40%
Protection class IEC	Safety class II	Packaging Material	Cardboard Plastic
Mechanical and Housing		Product Data	
Overall length	1,280 mm	Order product name	WT050C 2xTLED L1200
Overall width	93 mm	Full product name	WT050C 2xTLED L1200
Overall height	70 mm	Full product code	871016336603699
Dimensions (Height x Width x Depth)	70 x 93 x 1280 mm	Order code	911401807481
Material	Polycarbonate		
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]		
Mech. impact protection code	IK08 [5 J vandal-protected]		

Ledinaire Waterproof Tube Housing

Material Nr. (12NC)	911401807481	EAN/UPC - Case	8710163366197
Numerator - Quantity Per Pack	1		
EAN/UPC - Product/Case	8710163366036		
Numerator - Packs per outer box	12		

Dimensional drawing

WT050C L1200 2 Tube

