

WT050C 2xTLED L1200

911401807481



Ledinaire Waterproof Tube Housing, L1200 mm, IP65, IK08

L1200 mm, IP65 | Dust penetration-protected, jet-proof, IK08 | 5 J vandal-protected, Safety class II

General Information

Value ladder	Value
--------------	-------

Light Technical

Colour rendering index (CRI)	-
Luminaire light beam spread	-

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Protection class IEC	Safety class II

Mechanical and Housing

Overall length	1,280 mm
Overall width	93 mm

Overall height	70 mm
Dimensions (height x width x depth)	70 x 93 x 1280 mm
Material	Polycarbonate
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Accessory colour	Grey
Angle	-
Net Weight (Piece)	0.800 kg

Approval and Application


CE mark	Yes
EU RoHS compliant	Yes

Product Data


Order product name	WT050C 2xTLED L1200
Full product name	WT050C 2xTLED L1200
Full EOC	871016336603699
Order code	911401807481

Material no. (12 NC)	911401807481
Numerator – quantity per pack	1
EAN/UPC — Product/Case	8710163366036
Numerator – packs per outer box	12
EAN/UPC - Case	8710163366197

Dimensional drawing



Compatible Accessories

Accessory Image	Accessory Code	Accessory Name	Website
	929003519702	CorePro LEDtube 1200mm 15.5W 840 T8	Product Website

Related Documents

Documents and certificates	Document Name	Download
Installation Instructions	MI_WT050C_20200807_FINAL.pdf	Download

