



# Ledinaire Waterproof Tube Housing

## WT050C 2xTLED L1200

Ledinaire Waterproof Tube Housing, L1200 mm, IP65, IK08

L1200 mm, IP65 | Dust penetration-protected, jet-proof, IK08 | 5 J vandal-protected, Safety class II

### Product data

General Information	
Value ladder	Value

  

Light Technical	
Colour rendering index (CRI)	-
Luminaire light beam spread	-

  

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Protection class IEC	Safety class II

  

Mechanical and Housing	
Overall length	1,280 mm
Overall width	93 mm
Overall height	70 mm
Dimensions (height x width x depth)	70 x 93 x 1280 mm
Material	Polycarbonate
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]

  

Accessory colour	Grey
Angle	-
Net Weight (Piece)	0.800 kg

  

Approval and Application	
CE mark	Yes
EU RoHS compliant	Yes

  

Product Data	
Order product name	WT050C 2xTLED L1200
Full product name	WT050C 2xTLED L1200
Full EOC	871016336603699
Order code	911401807481
Material no. (12 NC)	911401807481
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8710163366036
Numerator – packs per outer box	12
EAN/UPC – Case	8710163366197

# Ledinaire Waterproof Tube Housing

## Dimensional drawing

WT050C L1200 2 Tube

