



Ledinaire Waterproof Tube Housing

WT050C 2xTLED L1500

Ledinaire Waterproof Tube Housing, L1500 mm, IP65, IK08

L1500 mm, IP65 | Dust penetration-protected, jet-proof, IK08 | 5 J vandal-protected, Safety class II

Product data

General Information	
Value ladder	Value

Light Technical	
Color rendering index (CRI)	-
Luminaire light beam spread	-

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Protection class IEC	Safety class II

Mechanical and Housing	
Overall length	1,580 mm
Overall width	93 mm
Overall height	70 mm
Dimensions (Height x Width x Depth)	70 x 93 x 1580 mm
Material	Polycarbonate
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]

Accessory color	Gray
Angle	-
Net Weight (Piece)	0.960 kg

Approval and Application	
CE mark	Yes
EU RoHS compliant	Yes

Sustainability Data	
Non-virgin material ratio of the packaging	Cardboard > 80% recycled Plastic >35% recycled
Packaging Recyclable content ratio	Cardboard recycling rate > 80% Plastic recycling rate > 40%
Packaging Material	Cardboard Plastic

Product Data	
Order product name	WT050C 2xTLED L1500
Full product name	WT050C 2xTLED L1500
Full product code	871016336605099
Order code	911401807681

Ledinaire Waterproof Tube Housing

Material Nr. (12NC)	911401807681	EAN/UPC - Case	8710163366210
Numerator - Quantity Per Pack	1		
EAN/UPC - Product/Case	8710163366050		
Numerator - Packs per outer box	12		

Dimensional drawing

WT050C L1500 2 Tube

