



# Ledinaire Waterproof Tube Housing

## WT050C 2xTLED L1500

Ledinaire Waterproof Tube Housing, L1500 mm, IP65, IK08

L1500 mm, IP65 | Dust penetration-protected, jet-proof, IK08 | 5 J vandal-protected, Safety class II

### Product data

General Information	
Value ladder	Value

  

Light Technical	
Color rendering index (CRI)	-
Luminaire light beam spread	-

  

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Protection class IEC	Safety class II

  

Mechanical and Housing	
Overall length	1,580 mm
Overall width	93 mm
Overall height	70 mm
Dimensions (Height x Width x Depth)	70 x 93 x 1580 mm
Material	Polycarbonate
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]

  

Accessory color	Gray
Angle	-
Net Weight (Piece)	0.960 kg

  

Approval and Application	
CE mark	Yes
EU RoHS compliant	Yes

  

Sustainability Data	
Non-virgin material ratio of the packaging	Cardboard > 80% recycled Plastic >35% recycled
Packaging Recyclable content ratio	Cardboard recycling rate > 80% Plastic recycling rate > 40%
Packaging Material	Cardboard Plastic

  

Product Data	
Order product name	WT050C 2xTLED L1500
Full product name	WT050C 2xTLED L1500
Full product code	871016336605099
Order code	36605099

## Ledinaire Waterproof Tube Housing

Material Nr. (12NC)	911401807681
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163366050
Numerator - Packs per outer box	12

EAN/UPC - Case	8710163366210
----------------	---------------

### Dimensional drawing

WT050C L1500 2 Tube

