



# Ledinaire Waterproof Tube Housing

## WT050C 2xTLED L1500

Ledinaire Waterproof Tube Housing, L1500 mm, IP65, IK08

L1500 mm, IP65 | Dust penetration-protected, jet-proof, IK08 | 5 J vandal-protected, Safety class II

### Product data

General Information		Accessory colour	Grey
Value ladder	Value	Angle	-
		Net Weight (Piece)	0.960 kg
Light Technical		Approval and Application	
Colour rendering index (CRI)	-	CE mark	Yes
Luminaire light beam spread	-	EU RoHS compliant	Yes
Operating and Electrical		Product Data	
Input Voltage	220 to 240 V	Order product name	WT050C 2xTLED L1500
Line Frequency	50 or 60 Hz	Full product name	WT050C 2xTLED L1500
Protection class IEC	Safety class II	Full EOC	871016336605099
Mechanical and Housing		Order code	911401807681
Overall length	1,580 mm	Material no. (12 NC)	911401807681
Overall width	93 mm	Numerator – quantity per pack	1
Overall height	70 mm	EAN/UPC – Product/Case	8710163366050
Dimensions (height x width x depth)	70 x 93 x 1580 mm	Numerator – packs per outer box	12
Material	Polycarbonate	EAN/UPC - Case	8710163366210
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]		
Mech. impact protection code	IK08 [5 J vandal-protected]		

# Ledinaire Waterproof Tube Housing

## Dimensional drawing

WT050C L1500 2 Tube

