



Smartbright T8 Batten

BN012C LED10/CW L600 G3

Smartbright T8 Batten, 10 W, 1000 lm, 6500 K

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. New T8 LED batten range is perfect replacement for traditional battens with fluorescent lamps. The process of selecting, installing, and maintaining is so easy – it's a simple switch. The range offer customer to choose from various options, standalone batten, Batten with individual switch and connectable Battens in addition to 3 CCTs and 2 Wattages.

Product data

| General Information | | Number of products on MCB of 16 A type B 10 | |
|------------------------------------|----------------------|---|-------------------------|
| Light source engine type | LED | Protection class IEC | Safety class II |
| Value ladder | Value | | |
| Light Technical | | Controls and Dimming | |
| Luminous Flux | 1,000 lm | Dimmable | No |
| Correlated Color Temperature (Nom) | 6500 K | Control interface | - |
| Luminous Efficacy (rated) (Nom) | 100 lm/W | | |
| Color rendering index (CRI) | >80 | Mechanical and Housing | |
| Light source color | 865 cool daylight | Housing Material | Polycarbonate |
| Effective projected area | 0.016 m ² | Optical cover material | Polycarbonate |
| Operating and Electrical | | Housing Color | White |
| Input Voltage | 220 to 240 V | Optical cover finish | Opal |
| Line Frequency | 50 or 60 Hz | Overall length | 574 mm |
| Inrush current | 9 A | Overall width | 28.4 mm |
| Power Consumption | 10 W | Overall height | 35.7 mm |
| Power Factor (Fraction) | 0.9 | Dimensions (Height x Width x Depth) | 36 x 28 x 574 mm |
| | | Ingress protection code | IP20 [Finger-protected] |
| | | Mech. impact protection code | IK02 [0.2 J standard] |

Smartbright T8 Batten

| | |
|--------------------|---------------|
| Optical cover type | Polycarbonate |
| Net Weight (Piece) | 0.151 kg |

Approval and Application

| | |
|---------------------------|---|
| Flammability mark | For mounting on normally flammable surfaces |
| CE mark | Yes |
| Ambient temperature range | -20 to +40 °C |

Initial Performance (IEC Compliant)

| | |
|-----------------------------|------------------------|
| Luminous flux tolerance | +/-10% |
| Initial chromaticity | 0.3123, 0.3282, SDCM≤6 |
| Power consumption tolerance | +/-10% |

Product Data

| | |
|---------------------------------|-------------------------|
| Order product name | BN012C LED10/CW L600 G3 |
| Full product name | BN012C LED10/CW L600 G3 |
| Full product code | 871951451783799 |
| Order code | 911401808382 |
| Material Nr. (12NC) | 911401808382 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8719514517837 |
| Numerator - Packs per outer box | 40 |
| EAN/UPC - Case | 8719514518049 |

Dimensional drawing

