



CoreLine Recessed Spot gen2

RS150Z CFRM RND-ADJUST D80 WH

CoreLine Recessed Spot gen2, Accessory, Aluminium, White, IK03 | 0.3 J

CoreLine Recessed Spot gen2 delivers on the CoreLine promise of innovative, easy to use and high-quality luminaires. Its modular design allows 'configure to fit' option that better responds to your specific needs. The range offers a wide range choice on light colour (CCT), light output, colour finish, frame types and connectivity options. The compact and lite design of CoreLine Recessed Spot gen2, always incorporating a push in connector allowing loop in/out wiring and supporting a wide range of wire diameters/cross-sectional area, makes installation hassle-free. High quality of light, numerous connectivity options, long luminaire lifetime and high system efficacy make CoreLine Recessed Spot gen2 an ideal accent solution for your indoor spot lighting applications.

Warnings and Safety

- The luminaire should be installed and disassembled by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements, as per the product mounting instructions.

Product data

General Information		Protection class IEC	
Value ladder	Performance		-
Operating and Electrical		Mechanical and Housing	
Input Voltage	- V	Overall height	29 mm
Line Frequency	- Hz	Overall diameter	95 mm
		Material	Aluminium
		Ingress protection code	-

CoreLine Recessed Spot gen2

Mech. impact protection code	IK03 [0.3 J]
Accessory colour	White
Angle	20°
Net Weight (Piece)	0.060 kg

Approval and Application

CE mark	Yes
EU RoHS compliant	Yes

Product Data

Order product name	RS150Z CFRM RND-ADJUST D80 WH
--------------------	-------------------------------

Full product name	RS150Z CFRM RND-ADJUST D80 WH
Full EOC	871951493847299
Order code	911401811684
Material no. (12 NC)	911401811684
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8719514938472
Numerator – packs per outer box	18
EAN/UPC – Case	8719514938588

