



# CoreLine Recessed Spot gen2

## RS150Z CFRM SQR-ADJUST D80 ALU

CoreLine Recessed Spot gen2, Accessory, Aluminium, Aluminium, IK03 | 0.3 J

CoreLine Recessed Spot gen2 delivers on the CoreLine promise of innovative, easy to use and high-quality luminaires. Its modular design allows 'configure to fit' option that better responds to your specific needs. The range offers a wide range choice on light colour (CCT), light output, colour finish, frame types and connectivity options. The compact and lite design of CoreLine Recessed Spot gen2, always incorporating a push in connector allowing loop in/out wiring and supporting a wide range of wire diameters/cross-sectional area, makes installation hassle-free. High quality of light, numerous connectivity options, long luminaire lifetime and high system efficacy make CoreLine Recessed Spot gen2 an ideal accent solution for your indoor spot lighting applications.

### Warnings and Safety

- The luminaire should be installed and disassembled by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements, as per the product mounting instructions.

### Product data

General Information		Protection class IEC	
Value ladder	Performance		-
Operating and Electrical		Mechanical and Housing	
Input Voltage	- V	Overall length	95 mm
Line Frequency	- Hz	Overall width	95 mm
		Overall height	29 mm
		Dimensions (height x width x depth)	29 x 95 x 95 mm

## CoreLine Recessed Spot gen2

Material	Aluminium
Ingress protection code	-
Mech. impact protection code	IK03 [0.3 J]
Accessory colour	Aluminium
Angle	20°
Net Weight (Piece)	0.060 kg

### Approval and Application

CE mark	Yes
EU RoHS compliant	Yes

### Product Data

Order product name	RS150Z CFRM SQR-ADJUST D80 ALU
--------------------	--------------------------------

Full product name	RS150Z CFRM SQR-ADJUST D80 ALU
Full EOC	871951493851999
Order code	911401812084
Material no. (12 NC)	911401812084
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8719514938519
Numerator – packs per outer box	18
EAN/UPC – Case	8719514938625

