



# Essential SmartBright LED Solar Flood

## BVC010 LED60/765 Solar

Solar flood light with lithium ferro phosphate battery built in the luminaire, Remote controller and installation accessories included. IP65, plastic housing. Available in 600, 1000, 2000, 3000, 4000, 5000 and 6000 Lumens

### Warnings and Safety

- Install the luminaire in a sunny place that is not shaded by trees, buildings and walls, then the solar panel can receive the maximum sunlight for charging the battery.
- Charge the product under sunlight for at least 8 hours before first time using.
- This luminaire does not need any external electrical connection. It works 100% on solar energy.

### Product data

General Information		Panel type	
Driver included	Yes	Panel type	Mono crystalline
Warranty period	1 years	Panel voltage	5 V
Light Technical		Panel peak wattage	20 W
Luminous Flux	6,000 lm	Charge controller type	PWM
Correlated Color Temperature (Nom)	6500 K	Cable connection kit	Included
Luminous Efficacy (rated) (Nom)	165 lm/W	Connection	-
Color rendering index (CRI)	70	Cable	-
Operating and Electrical		Grid connection type	Off grid
Line Frequency	- Hz	Controls and Dimming	
Battery type	LiFePO4	Dimmable	Preset Dimming
Battery ampere hour	16 Ah	Configurability	Not configurable
Battery voltage	3.2 V	Control interface	-
Battery charging & discharging cycles	500	Solar dimming profile	Preset Dimming

# Essential SmartBright LED Solar Flood

## Mechanical and Housing

Housing Color	Grey
Overall length	245 mm
Overall width	345 mm
Overall height	60 mm
Dimensions (Height x Width x Depth)	60 x 345 x 245 mm
Material	Acrylonitrile-butadiene-styrene
Battery location	Inbuilt luminaire
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Optical cover type	Polycarbonate
Net Weight (Piece)	3.200 kg

## Approval and Application

CE mark	Yes
EU RoHS compliant	Yes

Ambient temperature range	0 to +45 °C
<b>Product Data</b>	
Order product name	BVC010 LED60/765 Solar
Full product name	BVC010 LED60/765 Solar
Full product code	872110333711599
Order code	911401813003
Material Nr. (12NC)	911401813003
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8721103337115
Numerator - Packs per outer box	5
EAN/UPC - Case	8721103337566

## Dimensional drawing

