



Ledinaire High-bay

Highbay MB_Z

Ledinaire High-bay, Accessory

The Ledinaire highbay range contains a selection of off-the-shelf highbay LED luminaires that comes with the high Philips quality levels at a competitive price. Reliable, energy efficient and affordable. Ledinaire highbay enables, simple and flexible installation, either on a hook, or optional bracket. Products can be installed with optional reflectors for lower glare.

Product data

General Information	
Value ladder	Value
Operating and Electrical	
Input Voltage	- V
Line Frequency	- Hz
Protection class IEC	-
Mechanical and Housing	
Overall length	123.5 mm
Overall width	35 mm
Overall height	97 mm
Dimensions (Height x Width x Depth)	97 x 35 x 124 mm
Material	Steel
Ingress protection code	-
Mech. impact protection code	-
Net Weight (Piece)	0.220 kg
Approval and Application	
CE mark	Yes

EU RoHS compliant	Yes
Sustainability Data	
Non-virgin material ratio of the packaging	Cardboard > 80% recycled Plastic >35% recycled
Packaging Recyclable content ratio	Cardboard recycling rate > 80% Plastic recycling rate > 40%
Packaging Material	Cardboard Plastic
Product Data	
Order product name	Highbay MB_Z
Full product name	Highbay MB_Z
Full product code	872016975380899
Order code	911401813087
Material Nr. (12NC)	911401813087
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8721103304308
Numerator - Packs per outer box	20
EAN/UPC - Case	8720169753808

Ledinaire High-bay

Dimensional drawing

