

BVC010 LED40/730 Solar

911401814203



Solar Flood Light BVC010

Solar flood light with lithium ferro phosphate battery built in the luminaire, Remote controller and installation accessories included. IP65, plastic housing. Available in 600, 1000, 2000, 3000, 4000, 5000 and 6000 Lumens

Warnings and Safety

- Install the luminaire in a sunny place that is not shaded by trees, buildings and walls, then the solar panel can receive the maximum sunlight for charging the battery.
- Charge the product under sunlight for at least 8 hours before first time using.
- This luminaire does not need any external electrical connection. It works 100% on solar energy.

General Information

Driver included	Yes
Warranty period	1 years

Light Technical

Luminous Flux	4,000 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	165 lm/W
Color rendering index (CRI)	70

Operating and Electrical

Line Frequency	- Hz
Battery type	LiFePO4
Battery ampere hour	12 Ah
Battery voltage	3.2 V
Battery charging & discharging cycles	500
Panel type	Mono crystalline
Panel voltage	5 V
Panel peak wattage	12 W
Charge controller type	PWM
Cable connection kit	Included

Connection	-
Cable	-
Grid connection type	Off grid


Controls and Dimming

Dimmable	Preset Dimming
Configurability	Not configurable
Control interface	-
Solar dimming profile	Preset Dimming

Mechanical and Housing

Housing Color	Grey
Overall length	195 mm
Overall width	245 mm
Overall height	60 mm
Dimensions (Height x Width x Depth)	60 x 245 x 195 mm
Material	Acrylonitrile-butadiene-styrene
Battery location	Inbuilt luminaire
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]

Dimensional drawing



Optical cover type	Polycarbonate
Net Weight (Piece)	1.990 kg

Approval and Application

CE mark	Yes
EU RoHS compliant	Yes
Ambient temperature range	0 to +45 °C

Product Data

Order product name	BVC010 LED40/730 Solar
Full product name	BVC010 LED40/730 Solar
Full product code	872110333723899
Order code	911401814203
Material Nr. (12NC)	911401814203
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8721103337238
Numerator - Packs per outer box	5
EAN/UPC - Case	8721103337689

