



Essential SmartBright LED Solar Flood

BVC010 LED30/765 Solar Pro

Solar flood light with lithium ferro phosphate battery built in the luminaire, Remote controller and installation accessories included. IP65, plastic housing. Available in 600, 1000, 2000, 3000, 4000, 5000 and 6000 Lumens

Warnings and Safety

- Install the luminaire in a sunny place that is not shaded by trees, buildings and walls, then the solar panel can receive the maximum sunlight for charging the battery.
- Charge the product under sunlight for at least 8 hours before first time using.
- This luminaire does not need any external electrical connection. It works 100% on solar energy.

Product data

General Information		Panel type	
Driver included	Yes	Panel voltage	Mono crystalline
Warranty period	2 years	Panel peak wattage	5 V
Light Technical		Charge controller type	10 W
Luminous Flux	3,000 lm	Cable connection kit	PWM
Correlated Color Temperature (Nom)	6500 K	Connection	Included
Luminous Efficacy (rated) (Nom)	165 lm/W	Cable	-
Color rendering index (CRI)	70	Grid connection type	-
Operating and Electrical			Off grid
Line Frequency	- Hz	Controls and Dimming	
Battery type	LiFePO4	Dimmable	Preset Dimming
Battery ampere hour	8 Ah	Configurability	Not configurable
Battery voltage	3.2 V	Control interface	-
Battery charging & discharging cycles	1000	Solar dimming profile	Preset Dimming

Essential SmartBright LED Solar Flood

Mechanical and Housing

Housing Color	Grey
Overall length	160 mm
Overall width	215 mm
Overall height	53 mm
Dimensions (Height x Width x Depth)	53 x 215 x 160 mm
Material	Acrylonitrile-butadiene-styrene
Battery location	Inbuilt luminaire
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Optical cover type	Polycarbonate
Net Weight (Piece)	1.640 kg

Approval and Application

CE mark	Yes
EU RoHS compliant	Yes

Ambient temperature range	0 to +45 °C
---------------------------	-------------

Product Data

Order product name	BVC010 LED30/765 Solar Pro
Full product name	BVC010 LED30/765 Solar Pro
Full product code	872110333729099
Order code	911401814803
Material Nr. (12NC)	911401814803
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8721103337290
Numerator - Packs per outer box	5
EAN/UPC - Case	8721103337740

Dimensional drawing

