Essential Smartbright LED Batten

BN068C LED6/WW L600 TH G2

Essential Smartbright LED Batten, 6.5 W, 600 lm, 3000 K, Wide beam

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. This new batten range of LED products can be used to replace traditional battens with fluorescent lamps. The process of selecting, installing and maintaining is so easy – it's a simple switch

Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Light source engine type	LED
Value ladder	Value
Warranty period	1 years

Light Technical	
Luminous Flux	600 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	92 lm/W
Color rendering index (CRI)	>80
Light source color	Warm white
Optic type	Wide beam
Luminaire light beam spread	140°

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Power Consumption	6.5 W
Power Factor (Fraction)	0.5
Connection	Flying leads/wires
Cable	Cable without plug 2-pole
Number of products on MCB of 16 A type B	10
Protection class IEC	Safety class II

Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-

Essential Smartbright LED Batten

Constant light output	No
Maximum dim level	Not applicable

Mechanical and Housing

Housing Material	Polyamide
Optic material	Polycarbonate
Optical cover material	Polyamide
Fixation material	Steel
Housing Color	White
Optical cover finish	Clear
Overall length	585 mm
Overall width	21 mm
Overall height	34.2 mm
Dimensions (Height x Width x Depth)	34 x 21 x 585 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK00 [No protection]
Optical cover type	Polycarbonate linear
Net Weight (Piece)	0.087 kg

Approval and Application

Glow-wire test	Temperature 850 °C, duration 5 s
CE mark	No
EU RoHS compliant	Yes

Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<7
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Median useful life L70B50	20,000 hour(s)

Product Data

Order product name	BN068C LED6/WW L600 TH G2
Full product name	BN068C LED6/WW L600 TH G2
Full product code	911401820797
Order code	911401820797
Material Nr. (12NC)	911401820797
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163310619
Numerator - Packs per outer box	24
EAN/UPC - Case	8710163310916

Dimensional drawing



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.