PHILIPS

Lighting

Essential Smartbright waterproof

WT035C LED30/CW PSU GM CFW L1200

Essential Smartbright waterproof, 30 W, 3000 lm, 6500 K, 120°

Essential Smartbright slim waterproof

Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Light source engine type	LED
Value ladder	Value
Warranty period	2 years

Light Technical	
Luminous Flux	3,000 lm
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	90 lm/W
Color rendering index (CRI)	>70
Beam angle of light source	120 degree(s)
Light source color	865 cool daylight
Optic type	Beam angle 120°
Luminaire light beam spread	120°

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Inrush current	4 A
Inrush time	0.1 ms
Power Consumption	30 W
Power Factor (Fraction)	0.9
Connection	Connection unit 2-pole
Cable	Cable 0.25m without plug
Number of products on MCB of 16 A type B	24
Protection class IEC	Safety class II

Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No
Maximum dim level	Not applicable

Mechanical and Housing	
Housing Material	Polycarbonate
Reflector material	Steel
Optic material	Polycarbonate
Optical cover material	Polycarbonate

Essential Smartbright waterproof

Fixation material	-
Housing Color	White
Optical cover finish	Opal
Overall length	1,198 mm
Overall width	35.5 mm
Overall height	44.5 mm
Dimensions (Height x Width x Depth)	45 x 36 x 1198 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Optical cover type	Polycarbonate bowl/cover
Net Weight (Piece)	0.290 kg

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	-
CE mark	Yes
ENEC mark	-
EU RoHS compliant	No
Ambient temperature range	-20 °C to 40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	0.323 ; 0.35
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.004 %
Median useful life L70B50	20,000 hour(s)
Median useful life L80B50	15,610 hour(s)
Median useful life L90B50	7,330 hour(s)

Product Data

Order product name	WT035C LED30/CW PSU GM CFW L1200
Full product name	WT035C LED30/CW PSU GM CFW L1200
Full product code	871016334404199
Order code	911401821380
Material Nr. (12NC)	911401821380
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163344041
Numerator - Packs per outer box	24
EAN/UPC - Case	8710163344102

Dimensional drawing



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.