



CoreLine Recessed Spot gen2

RS155Z CFRM RND-FIX D68 WH

CoreLine Recessed Spot gen2, Accessory, Aluminum, White, IK03 | 0.3 J

CoreLine Recessed Spot gen2 delivers on the CoreLine promise of innovative, easy to use and high-quality luminaires. Its modular design allows “configure to fit” option that better responds to your specific needs. The range offers a wide range choice on light color (CCT), light output, color finish, frame types and connectivity options. The compact and lite design of CoreLine Recessed Spot gen2, always incorporating a push in connector allowing loop in/out wiring and supporting a wide range of wire diameters/cross-sectional area, makes installation hassle-free. High quality of light, numerous connectivity options, long luminaire lifetime and high system efficacy makes CoreLine Recessed Spot gen2 an ideal accent solution for your indoor spot lighting applications.

Warnings and Safety

- The luminaire should be installed and disassembled by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements, as per the product mounting instructions.

Product data

General Information		Protection class IEC	
Value ladder	Performance		-
Operating and Electrical		Mechanical and Housing	
Input Voltage	- V	Overall height	29 mm
Line Frequency	- Hz	Overall diameter	85 mm
		Material	Aluminum
		Ingress protection code	-

CoreLine Recessed Spot gen2

Mech. impact protection code	IK03 [0.3 J]
Accessory color	White
Angle	-
Net Weight (Piece)	0.040 kg

Approval and Application

CE mark	Yes
EU RoHS compliant	Yes

Product Data

Order product name	RS155Z CFRM RND-FIX D68 WH
--------------------	----------------------------

Full product name	RS155Z CFRM RND-FIX D68 WH
Full product code	871951494111399
Order code	911401823784
Material Nr. (12NC)	911401823784
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514941113
Numerator - Packs per outer box	18
EAN/UPC - Case	8719514941502

Dimensional drawing

