



# CoreLine Recessed Spot gen2

## RS155Z CFRM RND-ADJUST D70 ALU

CoreLine Recessed Spot gen2, Accessory, Aluminum, Aluminum, IK03 | 0.3 J

CoreLine Recessed Spot gen2 delivers on the CoreLine promise of innovative, easy to use and high-quality luminaires. Its modular design allows “configure to fit” option that better responds to your specific needs. The range offers a wide range choice on light color (CCT), light output, color finish, frame types and connectivity options. The compact and lite design of CoreLine Recessed Spot gen2, always incorporating a push in connector allowing loop in/out wiring and supporting a wide range of wire diameters/cross-sectional area, makes installation hassle-free. High quality of light, numerous connectivity options, long luminaire lifetime and high system efficacy makes CoreLine Recessed Spot gen2 an ideal accent solution for your indoor spot lighting applications.

### Warnings and Safety

- The luminaire should be installed and disassembled by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements, as per the product mounting instructions.

### Product data

General Information		Protection class IEC	
Value ladder	Performance		-
Operating and Electrical		Mechanical and Housing	
Input Voltage	- V	Overall height	29 mm
Line Frequency	- Hz	Overall diameter	85 mm
		Material	Aluminum
		Ingress protection code	-

## CoreLine Recessed Spot gen2

Mech. impact protection code	IK03 [0.3 J]
Accessory color	Aluminum
Angle	20°
Net Weight (Piece)	0.050 kg

### Approval and Application

CE mark	Yes
EU RoHS compliant	Yes

### Sustainability Data

Non-virgin material ratio of the packaging	Cardboard > 80% recycled
Packaging Recyclable content ratio	Cardboard recycling rate > 80%
Packaging Material	Cardboard

### Product Data

Order product name	RS155Z CFRM RND-ADJUST D70 ALU
Full product name	RS155Z CFRM RND-ADJUST D70 ALU
Full product code	871951494115199
Order code	911401824184
Material Nr. (12NC)	911401824184
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514941151
Numerator - Packs per outer box	18
EAN/UPC - Case	8719514941540

## Dimensional drawing

