



GreenPerform Waterproof G3

WT198C LED19S/840 PSU L600

GreenPerform Waterproof G3, 15 W, 1900 lm, 4000 K, 114°

GreenPerform Waterproof G3 is a superb choice for hard-working applications. Not only does it provide excellent optical performance, it also delivers substantial energy saving. And because it works seamlessly with IoT software like Interact, it also offers the option of customization, convenience, and data-driven insights.

Warnings and Safety

- UV radiation will damage the material over time resulting in loss of waterproof sealing and IP65 rating.
- Do not install the luminaire in locations where it will be exposed to direct sunlight.

Product data

General Information		Operating and Electrical	
Light source replaceable	No	Beam angle of light source	120 degree(s)
Number of gear units	1 unit	Light source color	840 neutral white
Driver included	Yes	Optic type	-
Light source engine type	LED	Luminaire light beam spread	114°
Service tag	Yes		
Value ladder	Performance	Input Voltage	220 to 240 V
Warranty period	3 years + 2 years upon registration	Line Frequency	50 or 60 Hz
		Initial CLO power consumption	- W
		Average CLO power consumption	- W
		Inrush current	3.58 A
		Inrush time	40 ms
		Power Consumption	15 W
		Power Factor (Fraction)	0.9
Light Technical			
Luminous Flux	1,900 lm		
Correlated Color Temperature (Nom)	4000 K		
Luminous Efficacy (rated) (Nom)	127 lm/W		
Color rendering index (CRI)	>80		

GreenPerform Waterproof G3

Connection	-
Cable	-
Number of products on MCB of 16 A type B	24
Protection class IEC	Safety class I

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No
Maximum dim level	Not applicable


Mechanical and Housing

Housing Material	Polycarbonate
Reflector material	Steel
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Stainless steel
Housing Color	Gray
Optical cover finish	Opal
Overall length	665 mm
Overall width	80 mm
Overall height	85 mm
Overall diameter	80 mm
Dimensions (Height x Width x Depth)	85 x 80 x 665 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Optical cover type	-
Net Weight (Piece)	0.800 kg

Approval and Application

Glow-wire test	Temperature 850 °C, duration 30 s
----------------	-----------------------------------

Dimensional drawing



Flammability mark	-
CE mark	Yes
ENEC mark	-
EU RoHS compliant	No
Ambient temperature range	-20 to +45 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38,0.38)
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	1 %
Median useful life L70B50	50,000 hour(s)
Median useful life L80B50	42,000 hour(s)
Median useful life L90B50	20,000 hour(s)

Product Data

Order product name	WT198C LED19S/840 PSU L600
Full product name	WT198C LED19S/840 PSU L600
Full product code	692234198271299
Order code	98271299
Material Nr. (12NC)	911401825580
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6922341982712
Numerator - Packs per outer box	9
EAN/UPC - Case	6922341982743

GreenPerform Waterproof G3

