



CoreLine Panel gen6

RC132A G6 29W 0.48-0.65A All In DS TD

CoreLine Panel gen6, Accessory

Philips CoreLine panel Gen6 delivers on the CoreLine promise of innovation, easy installation, and excellent illumination. Designed as a direct replacement for functional luminaires in general lighting applications, this LED panel light's innovative All-in feature offers a choice of three lumen packages and three-color temperatures in a single luminaire. This makes it easy to select the right product, gives you the flexibility respond to customer preferences on site, and means fewer product codes on stock. Installing the CoreLine RC132V LED panel is quick and easy, using the product's quick connector or flywire. The CoreLine range includes Interact Ready luminaires with integrated wireless communications, ready to be used with Interact gateways, sensors, and software.

Product data

General Information		Mech. impact protection code	
Value ladder	Performance		-
		Net Weight (Piece)	0.220 kg
Operating and Electrical		Approval and Application	
Input Voltage	200 to 240 V	CE mark	Yes
Line Frequency	50 or 60 Hz	EU RoHS compliant	Yes
Protection class IEC	Safety class II		
Mechanical and Housing		Product Data	
Overall length	450 mm	Order product name	RC132A G6 29W 0.48-0.65A All In DS TD
Overall width	67 mm	Full product name	RC132A G6 29W 0.48-0.65A All In DS TD
Overall height	34 mm	Full product code	872110333012399
Dimensions (Height x Width x Depth)	34 x 67 x 450 mm	Order code	911401830588
Material	Polycarbonate	Material Nr. (12NC)	911401830588
Ingress protection code	IP20 [Finger-protected]	Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8721103330123

CoreLine Panel gen6

Numerator - Packs per outer box	50
EAN/UPC - Case	8721103330154

Dimensional drawing

