



Essential SmartBright Solar Indoor Suspended

SP010P LED7/765

Solar indoor suspended do-it-yourself kit with integrated Lithium battery and a solar panel inside the packaging. On-board selector switch to chose among pre-set lighting modes.

Warnings and Safety

- This product includes rechargeable batteries which must be adequately charged under sunlight before use.

Product data

General Information	
Driver included	Yes
Value ladder	Value
Light Technical	
Luminous Flux	700 lm
Correlated Color Temperature (Nom)	6500 K
Color rendering index (CRI)	>70
Operating and Electrical	
Battery type	Lithiumion - NMC
Panel type	Poly crystalline
Panel voltage	5 V
Panel peak wattage	2 W
Grid connection type	Off grid

Controls and Dimming	
Dimmable	Yes
Configurability	Configurable
Solar dimming profile	On-board selector switch to chose from following pre-set modes - On 3Hrs Mode(Initial 700lumen 100%) ; 6Hrs Mode ; 12Hrs Mode ; SOS Flash ; Off
Mechanical and Housing	
Overall length	95 mm
Overall width	95 mm
Overall height	154 mm
Dimensions (Height x Width x Depth)	154 x 95 x 95 mm
Material	Acrylonitrile-butadiene-styrene
Battery location	In-built
Ingress protection code	IP20 [Finger-protected]
Optical cover type	Polycarbonate

Essential SmartBright Solar Indoor Suspended

Net Weight (Piece)	0.450 kg
Approval and Application	
Ambient temperature range	0 to +45 °C
Product Data	
Order product name	SP010P LED7/765
Full product name	SP010P LED7/765
Full product code	692382865656099

Order code	911401831902
Material Nr. (12NC)	911401831902
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828656560
Numerator - Packs per outer box	10
EAN/UPC - Case	6923828656638

Dimensional drawing

