



Essential SmartBright Solar Indoor Suspended

SP010P LED7/765

Solar indoor suspended do-it-yourself kit with integrated Lithium battery and a solar panel inside the packaging. On-board selector switch to chose among pre-set lighting modes.

Warnings and Safety

- This product includes rechargeable batteries which must be adequately charged under sunlight before use.

Product data

General Information		Controls and Dimming	
Driver included	Yes	Dimmable	Yes
Value ladder	Value	Configurability	Configurable
Light Technical		Solar dimming profile	On-board selector switch to chose from following pre-set modes - On 3Hrs Mode(Initial 700lumen 100%) ; 6Hrs Mode ; 12Hrs Mode ; SOS Flash ; Off
Luminous Flux	700 lm	Mechanical and Housing	
Correlated Color Temperature (Nom)	6500 K	Overall length	95 mm
Color rendering index (CRI)	>70	Overall width	95 mm
Operating and Electrical		Overall height	154 mm
Battery type	Lithiumion - NMC	Dimensions (Height x Width x Depth)	154 x 95 x 95 mm
Panel type	Poly crystalline	Material	Acrylonitrile-butadiene-styrene
Panel voltage	5 V	Battery location	In-built
Panel peak wattage	2 W	Ingress protection code	IP20 [Finger-protected]
Grid connection type	Off grid	Optical cover type	Polycarbonate

Essential SmartBright Solar Indoor Suspended

Net Weight (Piece)	0.450 kg
Approval and Application	
Ambient temperature range	0 to +45 °C
Product Data	
Order product name	SP010P LED7/765
Full product name	SP010P LED7/765
Full product code	692382865656099

Order code	911401831902
Material Nr. (12NC)	911401831902
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828656560
Numerator - Packs per outer box	10
EAN/UPC - Case	6923828656638

Dimensional drawing

