



# Essential SmartBright Solar Indoor Suspended

## SP010P LED7/765

Solar indoor suspended do-it-yourself kit with integrated Lithium battery and a solar panel inside the packaging. On-board selector switch to chose among pre-set lighting modes.

### Warnings and Safety

- This product includes rechargeable batteries which must be adequately charged under sunlight before use.

### Product data

General Information		Controls and Dimming	
Driver included	Yes	Dimmable	Yes
Value ladder	Value	Configurability	Configurable
Light Technical		Solar dimming profile	On-board selector switch to chose from following pre-set modes - On 3Hrs Mode(Initial 700lumen 100%) ; 6Hrs Mode ; 12Hrs Mode ; SOS Flash ; Off
Luminous Flux	700 lm	Mechanical and Housing	
Correlated Color Temperature (Nom)	6500 K	Overall length	95 mm
Color rendering index (CRI)	>70	Overall width	95 mm
Operating and Electrical		Overall height	154 mm
Battery type	Lithiumion - NMC	Dimensions (Height x Width x Depth)	154 x 95 x 95 mm
Panel type	Poly crystalline	Material	Acrylonitrile-butadiene-styrene
Panel voltage	5 V	Battery location	In-built
Panel peak wattage	2 W	Ingress protection code	IP20 [Finger-protected]
Grid connection type	Off grid	Optical cover type	Polycarbonate

## Essential SmartBright Solar Indoor Suspended

Net Weight (Piece)	0.450 kg
<b>Approval and Application</b>	
Ambient temperature range	0 to +45 °C
<b>Product Data</b>	
Order product name	SP010P LED7/765
Full product name	SP010P LED7/765
Full product code	692382865656099

Order code	911401831902
Material Nr. (12NC)	911401831902
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828656560
Numerator - Packs per outer box	10
EAN/UPC - Case	6923828656638

### Dimensional drawing

