



# Essential Smartbright Projector Gen 2

ST033T G2 LED5/930 7W I WB BK CN

Essential Smartbright Projector Gen 2, 7 W, 595 lm, 3000 K, 36°

Essential SmartBright Projector ST033T is a value for money product designed for Mass market trade. It is designed to replace halogen and CDM-standard-based projectors for retail and hospitality applications. This track based luminaire supports retailers to let their products stand out, or highlight certain objects. The clean and contemporary design with integrated driver, and choice in 24 or 36 degree beam angle makes the Essential SmartBright Projector relevant to many applications. The choice of 2 colors in White and Black helps the Retailer to choose products best suited to blend into the Store Environment. Compared to it's predecessor, it is not only cost effective, but also a more sleek and lighter product design. The product family includes 1M and 2M Track in Black and white color with I and L connector to support various applications.

## Product data

| General Information                |                 | Color rendering index (CRI) |                          |
|------------------------------------|-----------------|-----------------------------|--------------------------|
| Number of gear units               | 1 unit          | Color rendering index (CRI) | 90                       |
| Gear                               | EB [Electronic] | Number of light sources     | 1                        |
| Driver included                    | Yes             | Beam angle of light source  | 36 degree(s)             |
| Light source engine type           | LED             | Light source color          | 930 warm white           |
| Value ladder                       | Value           | Optic type                  | Beam angle 36° Wide beam |
|                                    |                 | Luminaire light beam spread | 36°                      |
|                                    |                 | Unified glare rating CEN    | Not applicable           |
|                                    |                 | Effective projected area    | 0.75 m <sup>2</sup>      |
| Light Technical                    |                 | Operating and Electrical    |                          |
| Luminous Flux                      | 595 lm          | Input Voltage               | 220-240 V                |
| Correlated Color Temperature (Nom) | 3000 K          |                             |                          |
| Luminous Efficacy (rated) (Nom)    | 85 lm/W         |                             |                          |

# Essential Smartbright Projector Gen 2

|  |                |
|--|----------------|
| Line Frequency                           | 50 or 60 Hz    |
| Inrush current                           | 6.64 A         |
| Inrush time                              | 0.074 ms       |
| Power Consumption                        | 7 W            |
| Power Factor (Fraction)                  | 0.5            |
| Connection                               | Track          |
| Cable                                    | -              |
| Number of products on MCB of 16 A type B | 117            |
| Suitable for random switching            | No             |
| Protection class IEC                     | Safety class I |

## Controls and Dimming

|                   |                |
|-------------------|----------------|
| Dimmable          | -              |
| Control interface | -              |
| Maximum dim level | Not applicable |

## Mechanical and Housing

|                              |                         |
|------------------------------|-------------------------|
| Housing Material             | Aluminium               |
| Reflector material           | -                       |
| Optic material               | Polycarbonate           |
| Optical cover material       | Polycarbonate           |
| Housing Color                | Black                   |
| Mounting device              | -                       |
| Optical cover finish         | Clear                   |
| Ingress protection code      | IP20 [Finger-protected] |
| Mech. impact protection code | IK03 [0.3 J]            |
| Optical cover type           | Polycarbonate           |
| Net Weight (Piece)           | 0.187 kg                |

## Approval and Application

|                                    |  |
|------------------------------------|--|
| Glow-wire test                     | Temperature 650 °C, duration 30 s              |
| Flammability mark                  | For mounting on normally flammable surfaces    |
| CE mark                            | No   |
| ENEC mark                          | -  |
| Photobiological risk               | Photobiological risk group 1 @200mm to EN62778 |
| EU RoHS compliant                  | Yes  |
| Performance ambient temperature Tq | 25 °C  |
| Ambient temperature range          | -20 °C to 45 °C                                |


## Initial Performance (IEC Compliant)

|                             |                    |
|-----------------------------|--------------------|
| Luminous flux tolerance     | -0%, +20%          |
| Initial chromaticity        | (0.44,0.40) SDCM<5 |
| Power consumption tolerance | +/-10%             |

## Product Data

|                                 |                                  |
|---------------------------------|----------------------------------|
| Order product name              | ST033T G2 LED5/930 7W I WB BK CN |
| Full product name               | ST033T G2 LED5/930 7W I WB BK CN |
| Full product code               | 692382867875399                  |
| Order code                      | 911401834387                     |
| Material Nr. (12NC)             | 911401834387                     |
| Numerator - Quantity Per Pack   | 1                                |
| EAN/UPC - Product/Case          | 6923828678753                    |
| Numerator - Packs per outer box | 48                               |
| EAN/UPC - Case                  | 6923828679033                    |

## Dimensional drawing



## Essential Smartbright Projector Gen 2

