



# GreenPerform Waterproof Tubular G2

## WT228C G2 LED70S/840 PSU L1500 TW

GreenPerform Waterproof Tubular G2, 43.5 W, 7000 lm, 4000 K, Fixed Output

GreenPerform Waterproof Tubular G2 delivers on the GreenPerform promise of innovative, high-quality luminaires. A reliable, efficient luminaire with long lifetime, GreenPerform Waterproof Tubular G2 comes in two versions to meet various applications needs. The ammonia-resistant and sealed luminaire (PMMA) is suitable for animal lighting, livestock and food applications, while the PC version offers a modern and industrial design that is suitable for a wide range of general lighting applications. Both versions come with significant dust, water and impact protection

### Warnings and Safety

- UV radiation will damage the material over time resulting in loss of waterproof sealing and IP rating.
- Do not install the luminaire in locations where it will be exposed to direct sunlight.

### Product data

General Information		Luminous Efficacy (rated) (Nom)	
Light source engine type	LED		161 lm/W
Value ladder	Performance	Color rendering index (CRI)	80
		Light source color	840 neutral white
		Unified glare rating CEN	30
Light Technical		Operating and Electrical	
Luminous Flux	7,000 lm	Input Voltage	220-240 V
Correlated Color Temperature (Nom)	4000 K		

## GreenPerform Waterproof Tubular G2

Line Frequency	50 or 60 Hz
Power Consumption	43.5 W
Power Factor (Fraction)	0.9
Number of products on MCB of 16 A type B 21	
Protection class IEC	Safety class I

### Controls and Dimming

Dimmable	No
Control interface	Fixed Output

### Mechanical and Housing

Housing Material	Plastic
Optical cover material	Polymethyl methacrylate
Housing Color	White RAL 9003
Optical cover finish	Opal
Ingress protection code	IP67 [Dust penetration-protected, watertight]
Mech. impact protection code	IK06 [1 J]
Optical cover type	Polymethyl methacrylate bowl/cover
Net Weight (Piece)	1.520 kg

### Approval and Application

CE mark	Yes
Ambient temperature range	-20 to +40 °C

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

### Product Data

Order product name	WT228C G2 LED70S/840 PSU L1500 TW
Full product name	WT228C G2 LED70S/840 PSU L1500 TW
Full product code	692382863539899
Order code	63539899
Material Nr. (12NC)	911401834688
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828635398
Numerator - Packs per outer box	6
EAN/UPC - Case	6923828635503

## Dimensional drawing

