



SmartBright Solar All-in-two Street Light

BRP216 LED40/740 G2 Solar

External high efficiency polysilicon solar panel Die-casting aluminum housing, Professional lighting distribution, 2000, 3000, 4000lumens versions available, Plug-play connector between luminaire and PV panel Inbuilt LiFePO4 battery and MPPT controller.

Warnings and Safety

- Install the luminaire in a sunny place that is not shaded by trees, buildings and walls, then the solar panel can receive the maximum sunlight for charging the battery.
- Charge the product under sunlight for at least 8 hours before first time using.
- This luminaire does not need any external electrical connection.
- It works 100% on solar energy.

Product data

General Information	
Driver included	Yes
Value ladder	Value
Warranty period	3 years
Light Technical	
Luminous Flux	4,000 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	180 lm/W
Color rendering index (CRI)	70
Operating and Electrical	
Battery type	Lithium Ferro Phosphate
Battery ampere hour	100 Ah

Battery voltage	3.2 V
Panel type	Poly crystalline
Panel voltage	16 V
Panel peak wattage	40 W
Grid connection type	Off grid
Controls and Dimming	
Dimmable	No
Configurability	Not configurable
Solar dimming profile	Pre-configured
Mechanical and Housing	
Housing Color	Gray
Overall length	583 mm

SmartBright Solar All-in-two Street Light

Overall width	218 mm
Overall height	96 mm
Dimensions (Height x Width x Depth)	96 x 218 x 583 mm
Material	Die-casting Aluminum
Battery location	In built
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Optical cover type	Polycarbonate
Net Weight (Piece)	7.900 kg

Approval and Application

Ambient temperature range	0 °C to 50 °C
---------------------------	---------------

Over Time Performance (IEC Compliant)

Median useful life L70B50	50,000 hour(s)
---------------------------	----------------

Application Conditions

Ambient temperature range for charging	0 °C to 50 °C
--	---------------

Ambient temperature range for discharging -10 °C to 60 °C
(when light is on)

Product Data

Order product name	BRP216 LED40/740 G2 Solar
Full product name	BRP216 LED40/740 G2 Solar
Full product code	692382866150200
Order code	911401845302
Material Nr. (12NC)	911401845302
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828661502
Numerator - Packs per outer box	1
EAN/UPC - Case	6923828661502

Dimensional drawing

