



Solar Panel Sub System

85Wp 21V Monocrystalline PV panel

A Range of Solar panels from 20 W to 325 W specially designed for Philips Solar Street lighting, Flood lighting and Solar Indoor Systems

Product data

General Information	
Value ladder	Value

Operating and Electrical	
Panel type	Mono crystalline
Panel voltage	21 V
Panel peak wattage	85 W

Mechanical and Housing	
Overall length	770 mm
Overall width	610 mm
Overall height	3 mm
Dimensions (Height x Width x Depth)	3 x 610 x 770 mm
Net Weight (Piece)	4.790 kg

Approval and Application	
Ambient temperature range	-40 °C to 85 °C

Product Data	
Order product name	85Wp 21V Monocrystalline PV panel
Full product name	85Wp 21V Monocrystalline PV panel
Order code	911401856702
Material Nr. (12NC)	911401856702
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	35

