



# Essential SmartBright G6 LED Floodlight

## BVP150 LED20/CW PSU 20W SWB G4 CN

Essential SmartBright G6 LED Floodlight, 2000 lm, 20 W, 865 cool daylight, 110°, Safety class I, Mounting bracket

Essential SmartBright G6 LED Floodlight is the new successor with robust die-cast aluminum housing and corrosion-proof coating which suitable for general outdoor application. Product has high efficacy which is energy saving for customers. Product has anti-siphon function to ensure a reliable performance in the long lifetime.

### Product data

General Information		Unified glare rating CEN	
Number of gear units	1 unit		Not applicable
Gear	EB [Electronic]	Effective projected area	0.009 m <sup>2</sup>
Driver included	Yes	Operating and Electrical	
Light source engine type	LED	Input Voltage	220 to 240 V
Warranty period	2 years	Line Frequency	50 or 60 Hz
Light Technical		Inrush current	2 A
Luminous Flux	2,000 lm	Inrush time	0.03 ms
Correlated Color Temperature (Nom)	6500 K	Power Consumption	20 W
Luminous Efficacy (rated) (Nom)	100 lm/W	Power Factor (Fraction)	0.9
Color rendering index (CRI)	≥80	Connection	Flying leads/wires
Number of light sources	1	Cable	Cable 0.3 m without plug
Beam angle of light source	110 degree(s)	Number of products on MCB of 16 A type B	106
Light source color	865 cool daylight	Suitable for random switching	No
Optic type	Reflector Symmetrical	Protection class IEC	Safety class I
Luminaire light beam spread	110°		

# Essential SmartBright G6 LED Floodlight

Controls and Dimming	
Dimmable	-
Control interface	-
Maximum dim level	Not applicable

Mechanical and Housing	
Housing Material	Aluminum die-cast
Reflector material	Polycarbonate
Optic material	Glass
Optical cover material	Tempered glass
Housing Color	Black
Mounting device	Mounting bracket
Optical cover finish	Clear
Overall length	129 mm
Overall width	121 mm
Overall height	23 mm
Dimensions (Height x Width x Depth)	23 x 121 x 129 mm
Ingress protection code	IP65 [Water-protected]
Mech. impact protection code	IK06 [1 J]
Optical cover type	Tempered glass
Net Weight (Piece)	0.260 kg

Approval and Application	
Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces


CE mark	Yes
ENEC mark	-
Photobiological risk	Photobiological risk group 1 @200mm to EN62778
Photobiological risk specification	0.2 m
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	-40 to +50 °C

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.31, 0.34) SDCM≤6
Power consumption tolerance	+/-10%

Product Data	
Order product name	BVP150 LED20/CW PSU 20W SWB G4 CN
Full product name	BVP150 LED20/CW PSU 20W SWB G4 CN
Full product code	692382863487299
Order code	911401860888
Material Nr. (12NC)	911401860888
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828634872
Numerator - Packs per outer box	36
EAN/UPC - Case	6923828635152

## Dimensional drawing

BVP150 G4 20W SWB



## Essential SmartBright G6 LED Floodlight

