



Solar Panel Sub System

330Wp 38V Polycrystalline PV panel

A Range of Solar panels from 20 W to 325 W specially designed for Philips Solar Street lighting, Flood lighting and Solar Indoor Systems

Product data

General Information		Approval and Application	
Value ladder	Value	Ambient temperature range	-40 °C to 85 °C
Operating and Electrical		Product Data	
Panel type	Poly crystalline	Order product name	330Wp 38V Polycrystalline PV panel
Panel voltage	38 V	Full product name	330Wp 38V Polycrystalline PV panel
Panel peak wattage	330 W	Order code	911401862002
Mechanical and Housing		Material Nr. (12NC)	911401862002
Overall length	1,956 mm	Numerator - Quantity Per Pack	1
Overall width	992 mm	Numerator - Packs per outer box	31
Overall height	3.5 mm		
Dimensions (Height x Width x Depth)	4 x 992 x 1956 mm		
Net Weight (Piece)	19.990 kg		

