



Solar Panel Sub System

220Wp 42V Monocrystalline PV panel

A Range of Solar panels from 20 W to 325 W specially designed for Philips Solar Street lighting, Flood lighting and Solar Indoor Systems

Product data

General Information	
Value ladder	Value
Operating and Electrical	
Panel type	Mono crystalline
Panel voltage	42 V
Panel peak wattage	220 W
Mechanical and Housing	
Overall length	1,580 mm
Overall width	705 mm
Overall height	3.5 mm
Dimensions (Height x Width x Depth)	4 x 705 x 1580 mm
Net Weight (Piece)	9.500 kg

Approval and Application	
Ambient temperature range	-40 °C to 85 °C
Product Data	
Order product name	220Wp 42V Monocrystalline PV panel
Full product name	220Wp 42V Monocrystalline PV panel
Order code	911401862802
Material Nr. (12NC)	911401862802
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	31

Solar Panel Sub System

Dimensional drawing

